



Соединительная шина

Тип EVG-3PHAS/16MODUL
Каталог № 285381

Abbildung ähnlich

Программа поставок

Основная функция		Сборная шина
Основная функция дополнительного оснащения		Сборная шина для линейного защитного автомата Сборная шина для дифференциальной защиты Сборная шина для переключателя комбинированной защиты FI/LS
Тип сборной шины		трехфазн.
Ассортимент		EVG

Технические характеристики согласно ETIM 7.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)		
Электротехника, электроника, системы автоматизации / Низковольтная коммутационная техника / Component for low-voltage switching technology / Phase busbar (ecI@ss10.0.1-27-37-13-06 [ACN992011])		
Number of phases		3
Number of poles		3
Suitable for number of devices		5
Pitch dimensions	mm	0
Cross section	mm ²	10
Length	mm	286
Number of modular spacings		16
Rated permanent current I _u	A	63
Type of electric connection		Fork
Insulated		Yes
Rated surge voltage	kV	4
Conditioned rated short-circuit current I _q	kA	25
Max. rated operation voltage U _e	V	415
Rated short-time withstand current I _{cw}	kA	0
Suitable for devices with N-busbar		No
Suitable for devices with auxiliary switch		No