

**Auxiliary contact, for PLS, postal Code, PKNM, ZP-A40...-  
ASA...IHK...WHK, Z-MS, 1N/O+1N/C, 0.5HP**

**Part no.** ZP-IHK  
286052  
**EL Number**  
(Norway) 1609488

General specifications		
Product name		Eaton Distribution parts
Part no.		ZP-IHK
EAN		4015082860523
Product Length/Depth		80 millimetre
Product height		75 millimetre
Product width		8.8 millimetre
Product weight		0.043 kilogram
Compliances		RoHS conform
Certifications		IEC 61373 EN45545-2
Product Tradename		None
Product Type		Distribution parts
Product Sub Type		None
Public Consumption		Yes
Product Family Description		ES-PMCC-PDC-Eaton Distribution parts
Globally Marketable		Yes
Product Specification Details		
Accessory/spare part type		Auxiliary contacts
Additional equipment required		Auxiliary switch
Ambient operating temperature - max		40 °C
Ambient operating temperature - min		-5 °C
Application		Switchgear for industrial and advanced commercial applications
Assembly width		0.5
Device fitting		Universal
EL number		1609488
Functions		Auxiliary switch
Number of contacts (change-over contacts)		0
Number of contacts (normally closed contacts)		1
Number of contacts (normally open contacts)		1
Number of poles at main contact unit - max		2
Number of switches (fault signal)		0
Rated operational voltage (Ue) - max		230 V
Rated switch current		3 A
Suitable for current of main contact unit - max		6 A
Type		Accessory Accessory for combined residual current/power circuit breaker Accessory for miniature circuit breaker
Used with		Auxiliary contacts Accessory for combined residual current/power circuit breaker Accessory for miniature circuit breaker Accessory
Voltage type		AC

## Technical data ETIM 8.0

Devices for distribution board-/surface mounting (EG000062) / Auxiliary device for distribution board devices (EC001286)		
Electric engineering, automation, process control engineering / Electrical installation, device / Breaker switch component / Auxiliary contact unit for distribution board (ec@ss10.0.1-27-14-35-02 [AKE327013])		
Device fitting		Universal
Additional equipment		Auxiliary switch

Installed at the factory		No
Width in number of modular spacings		0.5
Number of contacts as normally open contact		1
Number of contacts as normally closed contact		1
Number of contacts as change-over contact		0
Number of fault-signal switches		0
Rated switch current	A	3
Rated voltage	V	230
Voltage type for actuating		AC
With auto test for earth leakage function		No
Suitable for max. number of poles main contact unit (total)		2
Suitable for max. current main contact unit	A	6