



Motorová válcová pojistka, Střední napětí, 100 A, AC 3.6 kV, 50 kA, 51 x 254 mm, Archivace, BS, s úderníkem

Typ **3.6KV 100Amp 2" 'O' MOTORSTART FUSE**  
Catalog No. **3.6WDFH0100**

## Dodavatelský program

Produktový sortiment			Pojistka
Základní funkce			Motorová válcová pojistka
Oblast aplikace			Střední napětí
Stanovený proud	I	A	100
Jmenovité napětí			AC 3.6 kV
Velikost			51 x 254 mm
Kategorie užití			Archivace
Stavový indikátor			s úderníkem
Vypínací zatížitelnost		kA	50
použitelné pro velikost / aplikace			ochrana motoru
Standardní / schválení			BS
Tvar			válcové vyhnuté konce s otvory na šroub
Standardní/Regulace			BS2692-1 IEC 60282-1

## Technická data podle ETIM 7.0

Circuit breakers and fuses (EG000020) / Medium-/high voltage fuse (EC003507)			
Rated current		A	100
Rated voltage		kV	3.6
Voltage type			AC
Rated frequency		Hz	50 - 50
Breaking capacity		kA	50
Utilization category			Other
Application			Motor protection
Length		mm	254
Diameter		mm	51
Performance category according to IEC 60282-1			Back-up
With striker			Yes
Standard			British Standard
Release characteristic			Other
Installation technique			Air

## Další informace o produktech (propojení)

Product datasheet (pdf)	<a href="http://www1.cooperbusmann.com/pdf/4c55bf59-424e-4973-bb95-bd162228cca8.pdf">http://www1.cooperbusmann.com/pdf/4c55bf59-424e-4973-bb95-bd162228cca8.pdf</a>
-------------------------	---