



Motor fuse-link, medium voltage, 100 A, AC 3.6 kV, 50 kA, 51 x 254 mm, back-up, BS, with striker

Part no. 3.6KV 100Amp 2" 'O' MOTORSTART FUSE
Catalog No. 3.6WDFH0100

Delivery program

Product range			Fuse
Basic function			Motor fuse-link
Field of application			medium voltage
Rated current	I	A	100
Rated voltage			AC 3.6 kV
Size			51 x 254 mm
Utilization category			back-up
Status indicator			with striker
Breaking Capacity		kA	50
usable for size/applications			motor protection
Standard/Approval			BS
Shape			cylindrical offset bolted tags
Standards/Regulations			BS2692-1 IEC 60282-1

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Medium-/high voltage fuse (EC003507)			
Rated current		A	100
Rated voltage		kV	3.6
Voltage type			AC
Rated frequency		Hz	50 - 50
Breaking capacity		kA	50
Utilization category			Other
Application			Motor protection
Length		mm	254
Diameter		mm	51
Performance category according to IEC 60282-1			Back-up
With striker			Yes
Standard			British Standard
Release characteristic			Other
Installation technique			Air

Additional product information (links)

Product datasheet (pdf)	http://www1.cooperbusmann.com/pdf/4c55bf59-424e-4973-bb95-bd162228cca8.pdf
-------------------------	---