



Cable grommet, PG36

Part no. KT36
Catalog No. 033896

EL-Nummer (Norway) 4132345

Delivery program

Product range			General switchboard accessories
Accessories			Cable management
Accessories			Cable grommets
For use with			For wall thickness 2 - 8 mm
Material			Soft PVC cadmium- and lead-free
Surface finish			similar RAL 7035
Cable entry			PG 36
Hole diameter		mm	48
Outer cable diameter		mm	18 - 40
Example of application: NYM/NYY cable, 4-core		mm ²	10 - 70

Technical data

Material characteristics

Material			Soft PVC cadmium- and lead-free
----------	--	--	------------------------------------

Technical data ETIM 8.0

Cable and wire entry systems (EG000009) / Cable entry sleeve (EC000879)			
Electric engineering, automation, process control engineering / Electrical installation, device / Connection devices / Feed through spout (ecl@ss10.0.1-27-14-44-21 [AD1139007])			
Model			Closed
Suitable for cable gland			No
Cable entry			Round
Number of cables			1 - 1
Suitable for cable diameter		mm	18 - 40
Bore diameter		mm	48
For wall thickness		mm	2 - 8
Thread size (metric)			0
Thread size PG			36
Total length		mm	20
With strain relief			No
Shrink technique			No
Angle model			No
Material			Plastic
Material quality			Polyvinyl chloride (PVC)
Surface protection			Other
Halogen free			No
Colour			Grey
Gastight			Yes
Fire resistant			No
Watertight			Yes
Degree of protection (IP)			IP66
Operating temperature		°C	-5 - 40

Dimensions

