



**Fuse-link, low voltage, 40 A, AC 415 V, 33 kA, BS system C type II, 30 x 57 mm, gL/gG, BS**

**Part no. 40A 415V AC HOUSE SERVICE**  
**Catalog No. 40LR85**

### Delivery program

Product range			Fuse
Basic function			House service fuse-link
Field of application			low voltage
Rated current	I	A	40
Rated voltage			AC 415 V
Construction size			BS system C type II
Size			30 x 57 mm
Utilization category			gL/gG
Breaking Capacity		kA	33
usable for size/applications			protection of incoming cables into residential and commercial properties
Standard/Approval			BS
Shape			cylindrical
Standards/Regulations			BS88-3

### Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Cylindrical fuse (EC002704)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Cylindrical fuse (safety fuse) (ecl@ss10.0.1-27-14-20-02 [AFZ797013])			
Size			Other
Rated voltage		V	415 - 415
Rated voltage			Other
Voltage type			AC
Utilization category			gL/gG (cable protection/equipment protection)
Rated operating frequency		Hz	45 - 62
Nominal current		A	40
With striker			No
Release characteristic			Other
Breaking capacity		kA	33