

DATASHEET - 45AMP 690V TYPE T FUSE (10)



Fuse-link, high speed, 45 A, AC 690 V, DC 500 V, 200 kA, BS88, 18 x 96 mm, aR, BS, Special 80 mm fixing centres, thyristor fuse



Powering Business Worldwide™

Part no. 45AMP 690V TYPE T FUSE (10)
Catalog No. 45AFE

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	45
Rated voltage			AC 690 V DC 500 V
Construction size			BS88
Size			18 x 96 mm
Utilization category			aR
Description			Special 80 mm fixing centres thyristor fuse
Breaking Capacity		kA	200
usable for size/applications			DC common bus, DC drives, power converters/rectifiers and reduced voltage starters
Standard/Approval			BS
Shape			offset bolted tags (slotted)
Standards/Regulations			BS88-4 IEC 60269-4
Optional accessories			fuse-holder BH-0111

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	45
Rated voltage		V	690
Voltage type			AC/DC
Rated switching capacity		kA	200
Utilization category			aR (accompanied semiconductor protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No