



Motor fuse-link, medium voltage, 100 A, AC 5.5 kV, 60 kA, 76 x 403 mm, back-up, US, with striker, 3R

Part no. 5.5KV 3R USA FULL RANGE
Catalog No. 5.5VFNHA3R

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Motor fuse-link
Field of application			medium voltage
Rated current	I	A	100
Rated voltage			AC 5.5 kV
Size			76 x 403 mm
Utilization category			back-up
Status indicator			with striker
Breaking Capacity		kA	60
usable for size/applications			motor protection
Release characteristic	class		3R
Standard/Approval			US
Shape			cylindrical
Standards/Regulations			ANSI C37-46

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / Medium-/high voltage fuse (EC003507)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Safety fuse systems (unspecified) (ecl@ss10.0.1-27-14-21-90 [BAB265011])			
Rated current		A	100
Rated voltage		kV	5.5
Voltage type			AC
Rated frequency		Hz	60 - 60
Breaking capacity		kA	60
Utilization category			Other
Application			Motor protection
Length		mm	403
Diameter		mm	76
Performance category according to IEC 60282-1			Back-up
With striker			Yes
Standard			IEEE
Release characteristic			R
Installation technique			Air

Additional product information (links)

Product datasheet (pdf)	http://www1.cooperbusmann.com/pdf/4c55bf59-424e-4973-bb95-bd162228cca8.pdf
-------------------------	---