



Fuse-link, low voltage, 63 A, AC 500 V, 120 kA, NH000, gL/gG, IEC, dual indicator, live gripping lugs



**Part no.** NH FUSE 63AMP 500V SIZE 000 GG MGL  
**Catalog No.** 63NHG000B

**EL-Nummer (Norway)** 1664011

**Delivery program**

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	63
Rated voltage			AC 500 V
Construction size			NH000
Utilization category			gL/gG
Status indicator			dual indicator
Description			live gripping lugs
Breaking Capacity		kA	120
usable for size/applications			industrial
Standard/Approval			IEC
Shape			square body with knife blade contacts
Standards/Regulations			IEC 60269-2 fuse system A DIN 43620 VDE 0636-2

**Technical data ETIM 6.0**

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss8.1-27-14-20-05 [AFZ800012])			
Construction size			NH000
Nominal rated current		A	63
Nominal rated voltage		V	500
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			Combination fuse status indicator