



**Motor fuse-link, medium voltage, 100 A, AC 7.2 kV, 63 kA, 76 x 442 mm, back-up, BS, with striker**

**Part no. 7.2KV 100AMP MOTORSTART 3" FUSE 1242B**  
**Catalog No. 7.2WFMH7100**

### Delivery program

Product range			Fuse
Basic function			Motor fuse-link
Field of application			medium voltage
Rated current	I	A	100
Rated voltage			AC 7.2 kV
Size			76 x 442 mm
Utilization category			back-up
Status indicator			with striker
Breaking Capacity		kA	63
usable for size/applications			motor protection
Standard/Approval			BS
Shape			cylindrical offset bolted tags
Standards/Regulations			BS2692-1 IEC 60282-1

### Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / Medium-/high voltage fuse (EC003507)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Safety fuse systems (unspecified) (ecl@ss10.0.1-27-14-21-90 [BAB265011])			
Rated current		A	100
Rated voltage		kV	7.2
Voltage type			AC
Rated frequency		Hz	50 - 50
Breaking capacity		kA	63
Utilization category			Other
Application			Motor protection
Length		mm	442
Diameter		mm	76
Performance category according to IEC 60282-1			Back-up
With striker			Yes
Standard			DIN
Release characteristic			Other
Installation technique			Air

### Additional product information (links)

Product datasheet (pdf)	<a href="http://www1.cooperbussmann.com/pdf/4c55bf59-424e-4973-bb95-bd162228cca8.pdf">http://www1.cooperbussmann.com/pdf/4c55bf59-424e-4973-bb95-bd162228cca8.pdf</a>
-------------------------	---