



Motor fuse-link, medium voltage, 63 A, AC 7.2 kV, 63 kA, DIN 43625 3", 76 x 442 mm, back-up, DIN, with striker



Powering Business Worldwide™

Part no. 7.2KV 63AMP 3" DIN FUSE
Catalog No. 7.2WFMSJ63

Similar to illustration

Delivery program

| | | | |
|------------------------------|---|----|--|
| Product range | | | Fuse |
| Basic function | | | Motor fuse-link |
| Field of application | | | medium voltage |
| Rated current | I | A | 63 |
| Rated voltage | | | AC 7.2 kV |
| Construction size | | | DIN 43625 3" |
| Size | | | 76 x 442 mm |
| Utilization category | | | back-up |
| Status indicator | | | with striker |
| Breaking Capacity | | kA | 63 |
| usable for size/applications | | | motor protection |
| Standard/Approval | | | DIN |
| Shape | | | cylindrical |
| Standards/Regulations | | | DIN 43625 VDE 0670-4 IEC 60282-1 |

Technical data ETIM 8.0

| | | | |
|--|--|----|------------------|
| Circuit breakers and fuses (EG000020) / Medium-/high voltage fuse (EC003507) | | | |
| Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Safety fuse systems (unspecified) (ecl@ss10.0.1-27-14-21-90 [BAB265011]) | | | |
| Rated current | | A | 63 |
| Rated voltage | | kV | 7.2 |
| Voltage type | | | AC |
| Rated frequency | | Hz | 50 - 50 |
| Breaking capacity | | kA | 63 |
| Utilization category | | | Other |
| Application | | | Motor protection |
| Length | | mm | 442 |
| Diameter | | mm | 76 |
| Performance category according to IEC 60282-1 | | | Back-up |
| With striker | | | Yes |
| Standard | | | DIN |
| Release characteristic | | | Other |
| Installation technique | | | Air |

Additional product information (links)

| | |
|-------------------------|---|
| Product datasheet (pdf) | http://www1.cooperbusmann.com/pdf/4c55bf59-424e-4973-bb95-bd162228cca8.pdf |
|-------------------------|---|