

Motor fuse-link, medium voltage, 63 A, AC 7.2 kV, 63 kA, DIN 43625 3", 76 x 442 mm, back-up, DIN, with striker



Powering Business Worldwide™

Referencia **7.2KV 63AMP 3" DIN FUSE**
Catalog No. **7.2WFMSJ63**

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Motor fuse-link
Field of application			medium voltage
Rated current	I	A	63
Rated voltage			AC 7.2 kV
Construction size			DIN 43625 3"
Size			76 x 442 mm
Utilization category			back-up
Status indicator			with striker
Breaking Capacity		kA	63
usable for size/applications			motor protection
Standard/Approval			DIN
Shape			cylindrical
Standards/Regulations			DIN 43625 VDE 0670-4 IEC 60282-1

Technical data ETIM 7.0

Aparatos de protección y fusibles (EG000020) / Medium-/high voltage fuse (EC003507)			
Corriente nominal			63
Tensión nominal			7.2
Tipo de tensión			EV000460
Frecuencia nominal			50 - 50
Capacidad de desconexión			63
Categoría de uso			EV000154
Función			EV021971
Longitud			442
Diámetro			76
Con cebador			Yes
Tipo de disparo			EV000154
Sistema de instalación			EV021474

Additional product information (links)

Product datasheet (pdf)	http://www1.cooperbusmann.com/pdf/4c55bf59-424e-4973-bb95-bd162228cca8.pdf
-------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------