



Motorová válcová pojistka, Střední napětí, 80 A, AC 7.2 kV, 40 kA, 76 x 403 mm, Archivace, BS, s úderníkem



Powering Business Worldwide™

Typ 7.2KV 80A 3" MOTOR START FUSE
Catalog No. 7.2WFNH080

Dodavatelský program

Produktový sortiment			Pojistka
Základní funkce			Motorová válcová pojistka
Oblast aplikace			Střední napětí
Stanovený proud	I	A	80
Jmenovité napětí			AC 7.2 kV
Velikost			76 x 403 mm
Kategorie užití			Archivace
Stavový indikátor			s úderníkem
Vypínací zatížitelnost		kA	40
použitelné pro velikost / aplikace			ochrana motoru
Standardní / schválení			BS
Tvar			válcové vyhnuté konce s otvory na šroub
Standardní/Regulace			BS2692-1 IEC 60282-1

Technická data podle ETIM 8.0

Circuit breakers and fuses (EG000020) / Medium-/high voltage fuse (EC003507)			
Elektrotechnika, automatizační technika a technika řízení procesu / Elektroinstalacní zařízení, přístroj / Systémy tavných pojistek / Tavné pojistkové systémy (neklasifikováno) (ecl@ss10.0.1-27-14-21-90 [BAB265011])			
Rated current		A	80
Rated voltage		kV	7.2
Voltage type			AC
Rated frequency		Hz	50 - 50
Breaking capacity		kA	0.04
Utilization category			Other
Application			
Length		mm	76
Diameter		mm	
Performance category according to IEC 60282-1			Back-up
With striker			Yes
Standard			British Standard
Release characteristic			Other
Installation technique			Air

Další informace o produktech (propojení)

Product datasheet (pdf)	http://www1.cooperbusmann.com/pdf/4c55bf59-424e-4973-bb95-bd162228cca8.pdf
-------------------------	---