



**Fuse holder, low voltage, 50 A, AC 690 V, 14 x 51 mm, 1P, IEC, with indicator, replaces CH141BI**

**Referencia**                      **1P 14x51 Neon Indicator Fuse Holder**  
**Catalog No.**                      **CH141DIU**

## Delivery program

Product range			Fuse accessory
Basic function			Fuse-holder
Field of application			low voltage
Rated current	I	A	50
Rated voltage			AC 690 V
Size			14 x 51 mm
Status indicator			with indicator
Description			replaces CH141BI
Number of poles			1P
usable for size/applications			C14G fuses C14M fuses
Standard/Approval			IEC
Standards/Regulations			IEC 60269-1

## Technical data ETIM 7.0

Aparatos de protección y fusibles (EG000020) / Soporte para fusible cilíndrico (EC002705)		
Tecnología electrónica, de automatización y de mando de procesos / Instalación eléctricas, equipo / Sistema de fusibles / Holder for cylindrical fuse (ecl@ss10.0.1-27-14-21-21 [ADI305007])		
Tensión nominal	Volt	690
Método de montaje		Raíl DIN
Para tamaño de fusible		14 x 51 mm
Número de polos		1
Conmutación simultánea N-neutral		No
Bloqueable		Sí
Indicación de fallo óptico		Sí
Anchura según espacios de módulos		1.5
Profundidad	Millimeter	51.5
Grado de protección (IP)		IP20