



**Fuse holder, low voltage, 50 A, AC 690 V, 14 x 51 mm, 2P, IEC, with indicator, replaces CH142BI**

**Part no. 2P 14x51 Neon Indicator Fuse Holder**  
**Catalog No. CH142DIU**

## Delivery program

Product range			Fuse accessory
Basic function			Fuse-holder
Field of application			low voltage
Rated current	I	A	50
Rated voltage			AC 690 V
Size			14 x 51 mm
Status indicator			with indicator
Description			replaces CH142BI
Number of poles			2P
usable for size/applications			C14G fuses C14M fuses
Standard/Approval			IEC
Standards/Regulations			IEC 60269-1

## Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / Holder for cylindrical fuse (EC002705)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Holder for cylindrical fuse (ecl@ss10.0.1-27-14-21-21 [ADI305007])			
Nominal voltage		V	690
Mounting method			DIN rail
For fuse size			14x51 mm
Number of poles			2
Concurrently switching neutral conductor			No
Lockable			Yes
With optical defect indication			Yes
Width in number of modular spacings			3
Built-in depth		mm	51.5
Degree of protection (IP)			IP20