

DATASHEET - 4P 22X58 FUSE HOLDER



Fuse holder, low voltage, 125 A, AC 690 V, 22 x 58 mm, 4P, IEC, UL



Part no. **4P 22x58 Fuse Holder**
Catalog No. **CH224DU**

Delivery program

Product range			Fuse accessory
Basic function			Fuse-holder
Field of application			low voltage
Rated current	I	A	125
Rated voltage			AC 690 V
Size			22 x 58 mm
Protection			IP20
Number of poles			4P
usable for size/applications			C22M and C22G fuses
Standard/Approval			IEC UL
Standards/Regulations			IEC 60269-1 IEC 60269-2

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / Holder for cylindrical fuse (EC002705)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Holder for cylindrical fuse (ecl@ss10.0.1-27-14-21-21 [ADI305007])			
Nominal voltage		V	690
Mounting method			DIN rail
For fuse size			22x58 mm
Number of poles			4
Concurrently switching neutral conductor			No
Lockable			Yes
With optical defect indication			No
Width in number of modular spacings			8
Built-in depth		mm	51.5
Degree of protection (IP)			IP20