

DATASHEET - MFH 10x38 1 POLE FUSE LINK INDICATOR



Fuse holder, low voltage, 32 A, AC 690 V, 10 x 38 mm, 1P, IEC, with indicator



Part no. MFH 10x38 1 Pole Fuse link indicator
Catalog No. CHM1DUI-M

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Fuse-holder
Field of application			low voltage
Rated current	I	A	32
Rated voltage			AC 690 V
Size			10 x 38 mm
Status indicator			with indicator
Number of poles			1P
Standard/Approval			IEC
Standards/Regulations			IEC 60269-2

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / Holder for cylindrical fuse (EC002705)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Holder for cylindrical fuse (ec1@ss10.0.1-27-14-21-21 [ADI305007])			
Nominal voltage		V	690
Mounting method			DIN rail
For fuse size			10x38 mm
Number of poles			3
Concurrently switching neutral conductor			No
Lockable			No
With optical defect indication			No
Width in number of modular spacings			3
Built-in depth		mm	50
Degree of protection (IP)			IP20