



Fuse-link, low voltage, 30 A, AC 500 V, 200 kA, 10 x 38 mm, 13/32 x 1-1/2 inch, supplemental, UL, colour-coded, time-delay



Part no. **BUSS MIDGET FUSE**  
 Catalog No. **FNO-30**

### Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	30
Rated voltage			AC 500 V
Size			10 x 38 mm 13/32 x 1-1/2 inch
Utilization category			supplemental
Description			colour-coded
Breaking Capacity		kA	200
usable for size/applications			for motor control transformers and circuits with in-rush currents
Release characteristic	class		time-delay
Standard/Approval			UL
Shape			cylindrical
Material			fiber tube construction nickel-plated brass endcaps

### Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Cylindrical fuse (EC002704)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Cylindrical fuse (safety fuse) (ecl@ss10.0.1-27-14-20-02 [AFZ797013])			
Size			10x38 mm
Rated voltage		V	500 - 500
Rated voltage			Other
Voltage type			AC
Utilization category			Other
Rated operating frequency		Hz	45 - 62
Nominal current		A	30
With striker			No
Release characteristic			M (Midget)
Breaking capacity		kA	10

### Additional product information (links)

Product datasheet (PDF)	<a href="http://www.cooperindustries.com/content/dam/public/bussmann/Electrical/Resources/product-datasheets-a/Bus_Ele_DS_1012_FNO.pdf">http://www.cooperindustries.com/content/dam/public/bussmann/Electrical/Resources/product-datasheets-a/Bus_Ele_DS_1012_FNO.pdf</a>
-------------------------	---