



**Fuse-link, low voltage, 20 A, AC 600 V, 200 kA, 10 x 38 mm, 13/32 x 1-1/2 inch, CC, UL, rejection-type, time-delay**



**Part no. CLASS CC TIME DELAY REJECTION FUSE**  
**Catalog No. FNQ-R-20**

## Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	20
Rated voltage			AC 600 V
Size			10 x 38 mm 13/32 x 1-1/2 inch
Utilization category			CC
Description			rejection-type
Breaking Capacity		kA	200
usable for size/applications			branch circuit
Release characteristic	class		time-delay
Standard/Approval			UL
Shape			cylindrical

## Technical data ETIM 6.0

Circuit breakers and fuses (EG000020) / Cylindrical fuse (EC002704)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Cylindrical fuse (safety fuse) (ecl@ss8.1-27-14-20-02 [AFZ797010])			
Size			10x38 mm
Rated voltage			AC 600 V
Nominal current		A	20
With striker			No

## Additional product information (links)

Product datasheet (PDF)	<a href="http://www.cooperindustries.com/content/dam/public/bussmann/Electrical/Resources/product-datasheets-b/Bus_Ele_DS_1014_FNQ-R.pdf">http://www.cooperindustries.com/content/dam/public/bussmann/Electrical/Resources/product-datasheets-b/Bus_Ele_DS_1014_FNQ-R.pdf</a>
Product overview (WEB)	<a href="http://www.cooperindustries.com/content/public/en/bussmann/electrical/products/fuses_class_cc_j_rk1_rk5/class_cc/fnq-r1.html">http://www.cooperindustries.com/content/public/en/bussmann/electrical/products/fuses_class_cc_j_rk1_rk5/class_cc/fnq-r1.html</a>