

DATASHEET - 15AMP 1000V DC SOLAR FERRULE 10 X 38MM



Fuse-link, high speed, 15 A, DC 1000 V, 50 kA, IEC 60269-6 type A, 10 x 38 mm, gPV, UL PV, UL, IEC



Powering Business Worldwide™

Part no. 15AMP 1000V DC SOLAR FERRULE 10 X 38MM
Catalog No. PV-15A10F

EL-Nummer (Norway) 1600125

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	15
Rated voltage			DC 1000 V
Construction size			IEC 60269-6 type A
Size			10 x 38 mm
Utilization category			gPV UL PV
Breaking Capacity		kA	50
usable for size/applications			protection of solar PV strings
Standard/Approval			UL IEC
Shape			cylindrical
Standards/Regulations			IEC 60269-6 UL 2579
Optional accessories			fuse holder CHPV1U

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Cylindrical fuse (EC002704)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Cylindrical fuse (safety fuse) (ecl@ss10.0.1-27-14-20-02 [AFZ797013])			
Size			10x38 mm
Rated voltage		V	1000 - 1000
Rated voltage			Other
Voltage type			DC
Utilization category			Other
Rated operating frequency		Hz	0 - 0
Nominal current		A	15
With striker			No
Release characteristic			Other
Breaking capacity		kA	50