



Fuse-link, high speed, 15 A, DC 1000 V, 50 kA, IEC 60269-6 type A, 10 x 38 mm, gPV, UL PV, UL, IEC



Referencia **15AMP 1000V DC SOLAR FERRULE 10 X 38MM**
 Catalog No. **PV-15A10F**

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	15
Rated voltage			DC 1000 V
Construction size			IEC 60269-6 type A
Size			10 x 38 mm
Utilization category			gPV UL PV
Breaking Capacity		kA	50
usable for size/applications			protection of solar PV strings
Standard/Approval			UL IEC
Shape			cylindrical
Standards/Regulations			IEC 60269-6 UL 2579
Optional accessories			fuse holder CHPV1U

Technical data ETIM 7.0

Aparatos de protección y fusibles (EG000020) / Fusible cilíndrico (EC002704)			
Tecnología electrónica, de automatización y de mando de procesos / Instalación eléctricas, equipo / Inserto de fusibles / Fusibles cilíndricos (ecl@ss10.0.1-27-14-20-02 [AFZ797013])			
Tamaño			10 x 38 mm
Intervalo de tensión nominal		Volt	1000 - 1000
Tensión nominal (valor)			Otros
Tipo de tensión			CC
Categoría de uso			Otros
Intervalo de frecuencia de funcionamiento nominal		Hertz	0 - 0
Corriente nominal		Ampere	15
Con cebador			No
Tipo de disparo			Otros
Capacidad de desconexión		kiloamper	50