



**TWIN Surface-mounted installation distributor with DIN rail insert, IP55,
HxWxD=1200x615x265mm**



Part no. MDB-BI-12060/TWIN/DIN
Catalog No. 195384
EL-Nummer 1702813
(Norway)

Technical data ETIM 8.0

Distribution boards (EG000023) / Small distribution board (EC000214)			
Electric engineering, automation, process control engineering / Electrical installation, device / Electrical distribution system (incl. small distribution board) / Small distribution board (ecl@ss10.0.1-27-14-24-09 [ACN387011])			
Mounting method			Surface mounted (plaster)
Number of rows			6
Width in number of modular spacings			24
Type of cover			Door
Cover model			Closed
Transparent cover/door			No
Material housing			Aluminium
Height		mm	1200
Width		mm	615
Depth		mm	265
Built-in depth		mm	265
Built-in height		mm	1200
Built-in width		mm	615
Internal depth		mm	156
Earthing terminal block			Yes
Neutral terminal block			No
DIN-rail			Yes
With mounting plate			Yes
Extension possible			No
EMC-version			Yes
Colour			Grey
RAL-number			7035
Degree of protection (IP)			IP55
With lock			Yes
Type of closure			Other
Signal passing door			No