



Pipe fitting, cutting ring

**Part no. +E8-MCS
001624**

General specifications		
Product name		Eaton Moeller® series MCS Accessory Tube Fitting
Part no.		+E8-MCS
EAN		4015080016243
Product Length/Depth		100 millimetre
Product height		43 millimetre
Product width		90 millimetre
Product weight		0.16 kilogram
Certifications		CSA File No.: 012528 CSA CSA-CC22.2 No. 14 CSA Class No.: 3211-06
Product Tradename		MCS
Product Type		Accessory
Product Sub Type		Tube Fitting
Catalog Notes		Article no. for ordering with basic unit
General information		
Accessory/spare part type		Connection technique
Product category		Accessories
Type		Compression fitting
Climatic environmental conditions		
Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		70 °C

Technical data ETIM 9.0

Low-voltage industrial components (EG000017) / Accessories/spare parts for low-voltage switch technology (EC002498)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Component for low-voltage switching technology (accessories) (ecl@ss13-27-37-13-92 [AKN570018])		
Type of accessory/spare part		Connection technique
Accessory		Yes
Spare part		No