



Fuse-link, 10x38 mm, 8A, gG

Part no. Z-C10/SE-8A/GG
 Catalog No. 112160

Similar to illustration

Delivery program

Product range			Fuse material
Basic function			Accessories
Basic function			Cylindrical fuse inserts
Utilization category			Utilization category gG (gL)
Size			10 x 38
Rated operational current	I_e	A	8
Rated operational voltage	U_e	V AC	500

Technical data

Electrical

Standards			IEC 60269-1 IEC 60269-2-1
Rated operational voltage	U_e	V	
Rated operational voltage	U_e	V AC	500
	U_e	V AC	
Rated operating voltage	U_e	V AC	1 - 25 A: 500 32 A: 400
Rated frequency	f	Hz	50

Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	55

Technical data ETIM 5.0

Circuit breakers and fuses (EG000020) / Cylindrical fuse (EC002704)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Cylindrical fuse (safety fuse) (ecl@ss8-27-14-20-02 [AFZ797009])			
Size			10x38 mm
Rated voltage			-
Nominal current		A	8
With striker			No