



Дверь , IP55 , ДхШ = 1940x793mm

Тип XVTL-D-8-20
Каталог № 114651

Программа поставок

Ассортимент			Распределитель системы управления XVTL
Основная функция			Платы расширения
Функция продукции			Дополнительное оснащение
Принадлежности			Двери
Отдельное устройство/законченное устройство			Модульная система
Описание			замкнут Одностворчатые двери 3-точечное запирание с поворотным рычажным запором
Материал			Листовая сталь 1,25 мм
Качество поверхности			Полиэфирное порошковое покрытие RAL 7035, светло-серый RAL 9016, дорожный белый
Информация о комплекте поставки			включая винты
Класс защиты			IP55
подходит для ширины			800
подходит для высоты			2000

Технические характеристики согласно ETIM 5.0

Cabinet enclosures (EG000011) / Door/operating panel (switchgear cabinet) (EC000747)			
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Door (electrical cabinet) / Door/operating panel (enclosure) (ecl@ss8-27-18-22-04 [ACN614007])			
Model			Stop door
Version as glazed door			No
Version as door for disconnecting switch interlocking			No
Width		mm	793
Height		mm	1940
Depth		mm	40
EMC-version			Yes
Material			Steel
Type of surface			With powder coating
Colour			Grey
Degree of protection (IP)			IP55