



Power meter, 3N, 80A, MID

Part no. EME3P80MID
Catalog No. 167414
Alternate Catalog No. EME3P80MID

Similar to illustration

Technical data ETIM 6.0

Meters (EG000045) / Kilowatt-hour meter (EC001506)			
Electric engineering, automation, process control engineering / Electrical installation, device / Modular serial built-in device for electrical circuit distributors / Electronic electricity meter (ecl@ss8.1-27-14-23-16 [AFZ828011])			
Type of meter			Electromechanical
Rated current (In)		A	80
Max. current (Imax)		A	6
Rated voltage (Un) N-L		V	184 - 276
Rated voltage (Un) L-L		V	319 - 480
Frequency		Hz	50 - 50
Accuracy class			B
Pole type			Three conductor
Model			Direct measurement
Energy type			Effective power and blind power
Suitable for			Purchase/supply
Tariff type			Two-tariff
Tariff control			Internal
Measuring type load profile			No
Escapement mechanism			No
Calibrated			Yes
Approval			Measuring Instruments Directive
Pulse output			Electrical
Pulse type			S0
Pulse rate		Imp/kWh (kvarh)	0 - 0
Type of indication			Digital
Mounting method			DRA (DIN-rail adapter)
Width in number of modular spacings			4.1
Type of interface			Other
EEC40 signature			No
With lock code			Yes
Number of positions total (counter)			8
Degree of protection (IP)			IP20