



Connections, front, 2500A, IZMX40, 4 p, fixed mounted design

Part no. IZMX-TF404-2500F
 Catalog No. 173369
 Alternate Catalog No. RFADP4PFXF25

Delivery program

Accessories			Main terminal kits
Accessories			Front connections
Rated current	I_n	A	2000, 2500
Pole			4
For use with			IZMX40...4...20F IZMX40...4...25F INX40...4...20F INX40...4...25F
Information about equipment supplied			Each set includes the connections for top and bottom. 3-pole for 6 connections, 4-pole for 8 connections Screws, washers, and supports are included as standard.
Installation type			Fixed

Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	70

Technical data ETIM 5.0

Low-voltage industrial components (EG000017) / Connection vane/phase spreader (EC002019)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Connection vane/phase spreader (ecl@ss8-27-37-13-05 [ACN990008])			
Suitable for number of poles			4