

Referencia **CU12X5-2250**  
 Catalog No. **005093**

### Delivery program

Product range			60 mm system Compact system
Accessories			Flat copper bars
Single unit/Complete unit			Modular system
Description			Flat copper busbars
Surface finish			Tinned
Rated operational current	$I_e$	A	160
Length		mm	2250
For use with			SH0165/2
Cu factor		kg	1,20
<b>Copper busbars</b>			
Width		mm	12
Height		mm	5
Interval between busbar centres		mm	60
Material			Copper, tinned
<b>Notes</b>			
Calculating material allowance → General information chapter			
Selecting the busbar cross-section and the device to be used → Engineering chapter			

### Technical data

#### General

Standards			EN 13061
Interval between busbar centres		mm	60

#### Contacts

Interval between busbar centres		mm	60
Rated uninterrupted current			With temperature deviations, DIN 43671 stipulates that a correction factor k2 must be taken into account
Rated uninterrupted current	$I_u$	A	
$T_u = 35\text{ °C}$ and $T_s = 65\text{ °C}$			
with 12 x 5 mm bar	$I_u$	A	200
with 20 x 5 mm busbar	$I_u$	A	320
with 30 x 5 mm bar	$I_u$	A	450
with 12 x 10 mm bar	$I_u$	A	360
with 20 x 10 mm busbar	$I_u$	A	520
with 30 x 10 mm busbar	$I_u$	A	630

#### Electrical data

Rated operational current	$I_e$	A	160
---------------------------	-------	---	-----

#### Material characteristics

Material			Copper, tinned
Surface finish			Tinned

#### Notes

For rated uninterrupted current  $I_u$  of the contact the following applies: according to DIN 43671 correction factor k2 must be taken into account in case of different temperatures.

### Technical data ETIM 7.0

Conmutadores en baja tensión (EG000017) / Pletina (EC001522)			
Tecnología electrónica, de automatización y de mando de procesos / Tecnología de conmutación de baja tensión / Distribución de rieles (baja tensión) / Busbar (low-voltage switching technology) (ecl@ss10.0.1-27-37-03-03 [ACN949011])			
Entrada de intensidad nominal		Ampere	160

Modelo		Plano
Longitud		Millimeter2250
Anchura		Millimeter12
Altura		Millimeter5
Flexible		No
Tratamiento de superficie		Estañado