

Drive, on rear, 3p, lockable, red

Part no. **NZM1-XRAVR**
107249

General specifications		
Product name		Eaton Moeller series NZM operating element accessory
Part no.		NZM1-XRAVR
EAN		4015081070220
Product Length/Depth		145 millimetre
Product height		130 millimetre
Product width		115 millimetre
Product weight		0.56 kilogram
Compliances		IEC UL/CSA RoHS conform
Certifications		UL489 UL (Category Control Number DIHS) CSA (Class No. 1437-01) UL (File No. E140305) CSA (File No. 22086) UL listed CSA-C22.2 No. 5-09 CSA certified IEC60947 CE marking
Product Tradename		NZM
Product Type		Accessories
Product Sub Type		Operating element accessory
Delivery program		
Type		Accessory On rear drive
Features		Lockable
Special features		For direct rear connection of the switch to the side of the control panel or control panel door. Switch actuation on rear through side plate or control panel door. For switch with toggle lever
Frame		NZM1
Fitted with:		Extension shaft Padlock
Suitable for		Emergency stop Power circuit breaker Switch disconnecter
Used with		NZM1, N1, NS1, PN1
Technical Data - Mechanical		
Color		Red
Degree of protection / NEMA enclosure type		IP66 4X. 12
Locking facility		Lockable on the 0 position on the handle using up to 3 padlocks
Special features		For direct rear connection of the switch to the side of the control panel or control panel door. Switch actuation on rear through side plate or control panel door. For switch with toggle lever
Design verification as per IEC/EN 61439		
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.

10.3 Degree of protection of assemblies			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			Meets the product standard's requirements.
10.5 Protection against electric shock			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			Is the panel builder's responsibility.
10.8 Connections for external conductors			Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			Is the panel builder's responsibility.
10.10 Temperature rise			The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Handle for power circuit breaker (EC000229)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Handle for switch devices (ecl@ss10.0.1-27-37-04-14 [AKF012014])			
With restart blockage			No
With key lock			No
Padlock locking			Yes
Colour			Red
Suitable for emergency stop			Yes
With extension shaft			Yes
Suitable for power circuit breaker			Yes
Suitable for switch disconnecter			Yes
Degree of protection (NEMA)			4X, 12