



Touch panel, 24 V DC, 5.7z, TFTcolor, ethernet, RS232, RS485, CAN, (PLC)

Part no. **XV-102-D6-57TVR-10**
142531
EL Number **4521116**
(Norway)

General specifications		
Product name		Eaton XV-102 Touch panel
Part no.		XV-102-D6-57TVR-10
EAN		7640130096738
Product Length/Depth		170 millimetre
Product height		39 millimetre
Product width		130 millimetre
Product weight		0.54 kilogram
Certifications		IEC/EN 61000-6-4 UL report applies to both US and Canada CSA Class No.: N7GQ8 UL 60950-01 CUL508 UL 60950 EN 60950 DNV GL CSA-C22.2 No. 60950-1 Certified by UL for use in Canada UL File No.: E208621 UL Recognized UL Category Control No.: N7GQ2 CE IEC/EN 61131-2 IEC/EN 61000-6-2 EN 50178 EAC
Product Tradename		XV-102
Product Type		Touch panel
Product Sub Type		None
Catalog Notes		4-wire Technology 7 W for basic device + 2.5 W for USB module Can be expanded as required, see Accessories Can be fitted by user with article no. 142581 LIC-PLC-MXP-COMPACT Heat dissipation with power consumption for 24 V Optionally with SD card -> article no. 139807
Features & Functions		
Enclosure material		Plastic
Features		Ethernet interface Portrait format UL508, cUL approvals Fanless CPU and system cooling, natural convection-based passive cooling USB device Slot for SD card USB Host
Fitted with:		1 x USB device (built-in interface) 1 x RS485 (built-in interface) Message indication Message system (incl. buffer and confirmation) Recipes Alpha numeric keyboard Printer output 1 x CANopen®/easyNet (built-in interfaces) 1 x RS232 (built-in interface) Numeric keyboard 1 x Ethernet 10/100 Mbps (built-in interfaces) SW interfaces 1 x USB host 2.0 (built-in interface) Color display
Functions		Additional software components, loadable Process value representation (output) possible Process default value (input) possible
General information		
Battery runtime		Back-up of real-time clock: CR 2032 (190 mA/h), zero maintenance (soldered)
Conditions of acceptability		UL/CSA The following end-product enclosures are required: Fire The provided Ethernet Connection is only allowed to connect to inhouse networks. The investigated Pollution Degree is: 2

		The unit must be supplied via a SELV source.
Degree of protection		IP20, rear IP65
Degree of protection (front side)		NEMA 4X IP65
Fuse type		Built-in fuse (not accessible)
Lifespan		40,000 h (Service life of back-lighting)
Model		Insulating enclosure and front plate
Mounting method		Flush mounting - Inclination from vertical: $\pm 45^\circ$ (if using natural convection) Flush mounting - Clearance: Width x Height x Depth ≥ 30 mm (1.18") Flush mounting
Product category		HMI-PLC (SPS function, retrofittable)
Residual ripple		≤ 5 % (input voltage)
RoHs conformity		Yes
Software		XSOFT-CODESYS-3, PLC-Programming software, Engineering GALILEO, Visualization software, Engineering EPAM, Visualization software, Engineering XSOFT-CODESYS-2, Visualization software, Engineering XSOFT-CODESYS-3, Visualization software, Engineering XSOFT-CODESYS-2, PLC-Programming software, Engineering
Voltage type		DC
Ambient conditions, mechanical		
Shock resistance		Mechanical, According to IEC/EN 60068-2-27
Vibration resistance		According to IEC/EN 60068-2-6
Climatic environmental conditions		
Air pressure		795 - 1080 hPa (operation)
Ambient operating temperature - min		0 °C
Ambient operating temperature - max		50 °C
Operating temperature - min		0 °C
Operating temperature - max		50 °C
Relative humidity		10 - 95 % (non-condensing)
Electro magnetic compatibility		
Voltage dips		≤ 10 ms from rated voltage (24 V DC) 5 ms from undervoltage (19.2 V DC)
Electrical rating		
Permissible voltage		18 - 31.2 V DC, battery powered (rated operating voltage -25 %/+30 %) 18.0 - 31.2 V DC, absolute with ripple 35 V DC (for a duration of < 100 ms) 19.2 - 30 V DC, effective (rated operating voltage -20 %/+25 %)
Power consumption		9.5 W total 2.5 W (USB Slave to USB Host) Max. 10 W 7 W
Rated control supply voltage		24 V DC (UPOW, -20 %/+25 %) 24 V DC (UAUX, -20 %/+25 %)
Rated operational voltage		24 V DC (power-supply - safety extra low voltage)
Supply voltage at AC, 50 Hz - min		0 V AC
Supply voltage at AC, 50 Hz - max		0 V AC
Supply voltage at DC - min		20.4 V DC
Supply voltage at DC - max		28.8 V DC
Communication		
Interfaces		USB 2.0 device (not galvanically isolated) RS485 (not galvanically isolated, 9-pin SUB-D plug, UNC) CAN, not galvanically isolated (SUB-D plug 9 pole, UNC) USB 2.0 host (1.5 - 12 Mbit/s, not galvanically isolated) RS232 (not galvanically isolated, 9-pin SUB-D plug, UNC) Ethernet (100Base-TX/10Base-T)
Number of slots		1 (for SD-Card)
Protocol		Other bus systems CAN TCP/IP EtherNet/IP MODBUS
Display		
Display contrast ratio		300:1

Display lighting		LED Dimmable via software
Display size		115 x 86 mm
Display type		Color display, TFT Standard front with standard membrane (fully enclosed) TFT
Luminance intensity		250 cd/m ²
Number of colors of the display		65536
Screen size (diagonal)		5.7 in
Touch technology		Resistive touch Glass with film touch sensor Touch sensor (glass with foil), Resistive touch protective screen
Input/Output		
Resolution		640 x 480 px VGA
Safety		
Explosion safety category for dust		ATEX dust-ex-protection, II 3D Ex II T70°C IP5x: Zone 22, Category 3D ATEX dust-ex-protection, in relation to CE
Potential isolation		Supply voltage UAUX: no Power supply: no
Protection against polarity reversal		Yes, for supply voltage (Siemens MPI optional) Yes
System		
Backup time		10 years, typ. (time at zero voltage)
Memory		SD Memory Card Slot: SDA Specification 1.00 (External) 128 MByte internal NAND-Flash (can be used for data backup) 32 kByte internal NVRAM (retained data) 64 MByte internal DRAM (OS, Program and data memory)
Memory capacity		64,000 kByte
Operating system		Windows CE 5.0 (license included)
Processor		RISC CPU, 32 Bit, 400 MHz
Design verification		
Equipment heat dissipation, current-dependent P _{vid}		9.5 W
Heat dissipation capacity P _{diss}		0 W
Heat dissipation per pole, current-dependent P _{vid}		0 W
Rated operational current for specified heat dissipation (I _n)		0 A
Static heat dissipation, non-current-dependent P _{vs}		9.5 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Please enquire
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Meets the product standard's requirements.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 9.0

Programmable logic controllers PLC (EG000024) / Graphic panel (EC001412)		
Electric engineering, automation, process control engineering / Display and control component / Panel (HMI) / Graphic panel (HMI) (ecl@ss13-27-33-02-01 [AFX016008])		
Supply voltage AC 50 Hz	V	0 - 0
Supply voltage AC 60 Hz	V	0 - 0
Supply voltage DC	V	20.4 - 28.8
Voltage type (supply voltage)		DC
Power consumption	W	9.5
Number of HW-interfaces industrial Ethernet		1
Number of interfaces PROFINET		0
Number of HW-interfaces RS-232		1
Number of HW-interfaces RS-422		0
Number of HW-interfaces RS-485		1
Number of HW-interfaces serial TTY		0
Number of HW-interfaces USB		2
Number of HW-interfaces parallel		0
Number of HW-interfaces wireless		0
Number of HW-interfaces other		1
With SW interfaces		Yes
Supporting protocol for EtherCAT		No
Supporting protocol for TCP/IP		Yes
Supporting protocol for PROFIBUS		No
Supporting protocol for CAN		Yes
Supporting protocol for INTERBUS		No
Supporting protocol for ASI		No
Supporting protocol for KNX		No
Supporting protocol for Modbus		Yes
Supporting protocol for Data-Highway		No
Supporting protocol for DeviceNet		No
Supporting protocol for SUCONET		No
Supporting protocol for LON		No
Supporting protocol for PROFINET IO		No
Supporting protocol for PROFINET CBA		No
Supporting protocol for SERCOS		No
Supporting protocol for Foundation Fieldbus		No
Supporting protocol for EtherNet/IP		Yes
Supporting protocol for AS-Interface Safety at Work		No
Supporting protocol for DeviceNet Safety		No
Supporting protocol for INTERBUS-Safety		No
Supporting protocol for PROFIsafe		No
Supporting protocol for SafetyBUS p		No
Supporting protocol for other bus systems		Yes
Radio standard Bluetooth		No
Radio standard WLAN 802.11		No
Radio standard GPRS		No
Radio standard GSM		No
Radio standard UMTS		No
IO link master		No
Type of display		TFT
Colour display		Yes
Number of colours of the display		65536
Number of grey-scales/blue-scales of display		0
Screen diagonal	inch	5.7
Number of pixels, horizontal		640
Number of pixels, vertical		480

Useful project memory/user memory		kByte	64000
With numeric keyboard			Yes
With alpha numeric keyboard			Yes
Number of function buttons, programmable			0
Number of buttons with LED			0
Number of system buttons			1
Touch technology			Resistive touch
With message indication			Yes
With message system (incl. buffer and confirmation)			Yes
Process value representation (output) possible			Yes
Process default value (input) possible			Yes
With recipes			Yes
Number of password levels			200
With printer output			Yes
Number of online languages			100
Additional software components, loadable			Yes
Degree of protection (IP), front side			IP65
Degree of protection (NEMA), front side			4X
Certified for UL hazardous location class I			No
Certified for UL hazardous location class II			No
Certified for UL hazardous location class III			No
Certified for UL hazardous location division 1			No
Certified for UL hazardous location division 2			No
Certified for UL hazardous location group A (acetylene)			No
Certified for UL hazardous location group B (hydrogen)			No
Certified for UL hazardous location group C (ethylene)			No
Certified for UL hazardous location group D (propane)			No
Certified for UL hazardous location group E (metal dusts)			No
Certified for UL hazardous location group F (carbonaceous dusts)			No
Certified for UL hazardous location group G (non-conductive dusts)			No
Operating temperature		°C	0 - 50
Rail mounting possible			No
Wall mounting/direct mounting			No
Suitable for safety functions			No
Width of the front		mm	170
Height of the front		mm	130
Built-in depth		mm	34