

Tunnel terminal, 3p, 6x16mm², +cover



Part no. NZM1-XKAM
144112
EL Number 4358623
(Norway)

Product name	Eaton Moeller series NZM connection type
Part no.	NZM1-XKAM
EAN	4015081406289
Product Length/Depth	80 millimetre
Product height	59 millimetre
Product width	90 millimetre
Product weight	0.27 kilogram
Compliances	UL/CSA IEC RoHS conform
Product Tradename	NZM
Product Type	Accessories
Product Sub Type	Connection type
Type	Accessory Terminal Tunnel terminal
Number of poles	Three-pole
Amperage Rating	≤ 160 A
Frame	NZM1
Suitable for	Aluminum cable Three-pole Copper cable
Used with	NZM1, PN1, N(S)1
Terminal capacity (stranded cable)	2.5 mm ² - 16 mm ² (6x) at digital input of supply connection 6 - 14 AWG/kcmil (6x)
10.2.2 Corrosion resistance	Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures	Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat	Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects	Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation	Meets the product standard's requirements.
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of assemblies	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.
10.10 Temperature rise	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Model		Other
-------	--	-------

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Wiring set for power circuit breaker (EC002050)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Wiring set for circuit breaker (ecl@ss10.0.1-27-37-04-24 [ACN957011])		
Suitable for number of poles		3
Model		Other