



**Main switch assembly kit, handle black, +additional handle, shaft 600mm**

**Part no. NZM1-XHB-DA-V6  
144905**

General specifications		
Product name		Eaton Moeller series NZM operating element
Part no.		NZM1-XHB-DA-V6
EAN		4015081414154
Product Length/Depth		580 millimetre
Product height		100 millimetre
Product width		140 millimetre
Product weight		0.795 kilogram
Compliances		RoHS conform UL/CSA IEC
Product Tradename		NZM
Product Type		Accessories
Product Sub Type		Operating element
Delivery program		
Type		Accessory Main switch assembly kit
Features		With black door coupling rotary handle Lockable
Special features		External warning plate/designation label can be clipped on. For enhanced busbar tag shroud on the incomer side, please order IP2X protection against contact with a finger. Kit for use as a main switch
Frame		NZM1
Fitted with:		Padlock Extension shaft Black and yellow lightning symbol External warning plate/markings plate in German/English Extension shaft NZM...-XV6 for mounting depth 600 mm Door coupling rotary handle with rotary drive Add-on rotary handle on switch with "Deliberate Action" operation as per NFPA79 and UL508A Part 2
Suitable for		Switch disconnecter Power circuit breaker
Used with		N(S)1(-4) PN1(-4) NZM1(-4)
Technical Data - Mechanical		
Color		Black
Cover/door type		After the door interlock is activated, must not be opened while on ON or TRIP. Must only be opened on OFF Door interlock can be modified such that it can be defeated from the outside using a screwdriver Door interlock not defeated in the locked OFF position. Door interlock on OFF with max. 3 padlocks
Degree of protection / NEMA enclosure type		4X, 12 IP66
Locking facility		Lockable on the 0 position on the switch using up to 3 padlocks
Special features		External warning plate/designation label can be clipped on. For enhanced busbar tag shroud on the incomer side, please order IP2X protection against contact with a finger. Kit for use as a main switch
Design verification as per IEC/EN 61439		
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.

10.3 Degree of protection of assemblies			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			Meets the product standard's requirements.
10.5 Protection against electric shock			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			Is the panel builder's responsibility.
10.8 Connections for external conductors			Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			Is the panel builder's responsibility.
10.10 Temperature rise			The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

## Technical data ETIM 9.0

Low-voltage industrial components (EG000017) / Handle for power circuit breaker (EC000229)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Handle for switch devices (ecl@ss13-27-37-04-14 [AKF012019])			
With restart blockage			No
With key lock			No
Padlock locking			Yes
Colour			Black
Suitable for emergency stop			No
With extension shaft			Yes
Suitable for power circuit breaker			Yes
Suitable for switch disconnecter			Yes
Degree of protection (NEMA)			4X, 12