



Touch panel, 24 V DC, 8.4z, TFTcolor, ethernet, RS232, RS485, profibus, PLC



Part no. **XV-152-D8-84TVRC-10**
150606
EL Number **4521151**
(Norway)

General specifications	
Product name	Eaton XV-152 Touch panel
Part no.	XV-152-D8-84TVRC-10
EAN	7640130097247
Product Length/Depth	275 millimetre
Product height	52.5 millimetre
Product width	208 millimetre
Product weight	2.15 kilogram
Certifications	IEC/EN 61000-6-3 UL Category Control No.: NRAQ CUL508 IEC/EN 60079-0 (ATEX 94/9/EG: Zone 22, Category 3D (II 3D Ex tc IIIC T70°C IP6x) IEC/EN 61000-6-2 CSA File No.: UL report applies to both US and Canada Security: EN 60950 CULus UL File No.: E205091 IEC/EN 61131-2 Certified by UL for use in Canada IEC/EN 60950 IEC/EN 61131-2, CE EN 50178 ATEX 94/9/EG: Zone 22, Category 3D (II 3D Ex tc IIIC T70°C IP6x) UL UL508 IEC/EN 61000-6-4 CSA Class No.: none UL 508 UL 60950 IEC/EN 61241-1 (ATEX 94/9/EG: Zone 22, Category 3D (II 3D Ex tc IIIC T70°C IP6x) DNV GL IEC/EN 61241-0 (ATEX 94/9/EG: Zone 22, Category 3D (II 3D Ex tc IIIC T70°C IP6x)
Product Tradename	XV-152
Product Type	Touch panel
Product Sub Type	None
Catalog Notes	12 W for basic device + 2.5 W for USB module 4-wire Technology Heat dissipation with power consumption for 24 V License certificates for onboard interfaces not required Optionally with SD card -> article no. 139807 PLC license inclusive
Features & Functions	
Enclosure material	Metal, anodized
Features	Fanless CPU and system cooling, natural convection-based passive cooling USB device USB Host Ethernet interface Overload proof Portrait format UL508, cUL approvals Slot for SD card
Fitted with:	Recipes Alpha numeric keyboard 1 x PROFIBUS/MPI (built-in interface) 1 x RS485 (built-in interface) Message system (incl. buffer and confirmation) 1 x USB device (built-in interface) 1 x Ethernet 10/100 Mbps (built-in interfaces) 1 x USB host 2.0 (built-in interface) SW interfaces Color display 1 x RS232 (built-in interface) Numeric keyboard Message indication Printer output
Functions	Process default value (input) possible Additional software components, loadable Process value representation (output) possible

General information	
Battery runtime	Back-up of real-time clock: CR 2032 (190 mA/h), zero maintenance (soldered)
Current consumption	0.6 A, continuous current, Power Supply, 24 V DC
Degree of protection	NEMA 4X IP20 IP20, rear
Degree of protection (front side)	IP65 NEMA 4X
Fuse type	Built-in fuse (not accessible)
Lifespan	40,000 h (Service life of back-lighting)
Model	Metal enclosure and front plate
Mounting method	Flush mounting - Inclination from vertical: $\pm 45^\circ$ (if using natural convection) Flush mounting Flush mounting - Clearance: Width x Height x Depth ≥ 30 mm (1.18")
Product category	HMI-PLC (integrated SPS function)
Repetition rate	1 s
Residual ripple	≤ 5 % (input voltage)
RoHS conformity	Yes
Short-circuit protection	Yes, Short-circuit rating, SmartWire-DT supply voltage No, external fuse FAZ Z3, Supply voltage UAux
Software	EPAM, Visualization software, Engineering GALILEO, Visualization software, Engineering XSOF-CODESYS-2, Visualization software, Engineering XSOF-CODESYS-3, PLC-Programming software, Engineering XSOF-CODESYS-3, Visualization software, Engineering XSOF-CODESYS-2, PLC-Programming software, Engineering
Terminal capacity	0.25 - 1.5 mm ² , flexible with ferrule 0.2 - 1.5 mm ² , solid 24 - 16 AWG, solid or stranded
Voltage type	DC
Ambient conditions, mechanical	
Shock resistance	Mechanical, According to IEC/EN 60068-2-27
Vibration resistance	According to IEC/EN 60068-2-6
Climatic environmental conditions	
Air pressure	795 - 1080 hPa (operation)
Ambient operating temperature - min	0 °C
Ambient operating temperature - max	50 °C
Ambient storage temperature - min	-20 °C
Ambient storage temperature - max	60 °C
Operating temperature - min	0 °C
Operating temperature - max	50 °C
Relative humidity	IEC/EN 50178 10 - 95 % (non-condensing)
Electro magnetic compatibility	
Voltage dips	≤ 10 ms from rated voltage (24 V DC) ≤ 10 ms, Bridging voltage dips 5 ms from undervoltage (19.2 V DC)
Electrical rating	
Inrush current	12.5 A (for 6 ms)
Permissible voltage	18 - 31.2 V DC, battery powered (rated operating voltage -25 %/+30 %) 19.2 - 30 V DC, effective (rated operating voltage -20 %/+25 %) 18.0 - 31.2 V DC, absolute with ripple 35 V DC (for a duration of < 100 ms)
Power consumption	9.5 W total Max. 12 W 2.5 W (USB Slave to USB Host) 12 W
Rated control supply voltage	24 V DC (UPOW, -20 %/+25 %) 24 V DC (UAUX, -20 %/+25 %)
Rated operational current (Ie)	0.7 A
Rated operational voltage	14.5 V (± 3 % - SmartWire-DT) 24 V DC (power-supply - safety extra low voltage)
Supply current	3 A, I _{max} , Supply voltage UAux 0.7 A, I _{max} , SmartWire-DT supply
Supply voltage at AC, 50 Hz - min	0 V AC

Supply voltage at AC, 50 Hz - max		0 V AC
Supply voltage at DC - min		20.4 V DC
Supply voltage at DC - max		28.8 V DC
Communication		
Addressing		Address set automatically
Connection		SmartWire-DT blade terminal SWD4-8MF2
Connection type		SWD: Plug, 8-pole Push in terminals, Supply voltage
Data transfer rate		125 kBit/s, SmartWire-DT 250 kBit/s, SmartWire-DT
Interfaces		USB 2.0 device (not galvanically isolated) Ethernet (100Base-TX/10Base-T)
LED indicator		Status indication of Supply voltage: LED Status indication of SmartWire-DT master: Green and red LEDs Status indication of SmartWire-DT network: Configurable green or red LED
Number of slots		1 (for SD-Card)
Number of SmartWire-DT slaves		58
Protocol		EtherNet/IP MODBUS TCP/IP Other bus systems PROFIBUS
Station		SmartWire-DT master, SmartWire-DT network
Display		
Display contrast ratio		300:1
Display lighting		LED Dimmable via software
Display size		170 x 128 mm
Display type		TFT Standard front with standard membrane (fully enclosed) Color display, TFT
Luminance intensity		250 cd/m ²
Number of colors of the display		65536
Screen size (diagonal)		8.4 in
Touch technology		Resistive touch Glass with film touch sensor Touch sensor (glass with foil), Resistive touch protective screen
Input/Output		
Resolution		640 x 480 px VGA
Safety		
Explosion safety category for dust		ATEX dust-ex-protection, II 3D Ex II T70°C IP5x: Zone 22, Category 3D ATEX dust-ex-protection, in relation to CE
Potential isolation		UAUX: no Power supply: no Between UPow and 15 V SmartWire-DT supply voltage: no
Protection against polarity reversal		Yes Yes, for supply voltage (Siemens MPI optional)
System		
Backup time		10 years, typ. (time at zero voltage)
Memory		NAND-Flash (can be used for data backup): approx. 64 MByte available NOR-Flash: 2 MByte 64 MByte internal DRAM (OS, Program and data memory) SD Memory Card Slot: SDA Specification 1.00 (External) NVRAM (Retain data): 125 kByte
Memory capacity		64,000 kByte
Operating system		Windows CE 5.0 (license included)
Processor		RISC CPU, 32 Bit, 400 MHz
Design verification		
Equipment heat dissipation, current-dependent Pvid		14.5 W
Heat dissipation capacity Pdis		0 W
Heat dissipation per pole, current-dependent Pvid		0 W
Rated operational current for specified heat dissipation (In)		0 A
Static heat dissipation, non-current-dependent Pvs		14.5 W

10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Please enquire
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Meets the product standard's requirements.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 9.0

Programmable logic controllers PLC (EG000024) / Graphic panel (EC001412)		
Electric engineering, automation, process control engineering / Display and control component / Panel (HMI) / Graphic panel (HMI) (ecl@ss13-27-33-02-01 [AFX016008])		
Supply voltage AC 50 Hz	V	0 - 0
Supply voltage AC 60 Hz	V	0 - 0
Supply voltage DC	V	20.4 - 28.8
Voltage type (supply voltage)		DC
Power consumption	W	9.5
Number of HW-interfaces industrial Ethernet		1
Number of interfaces PROFINET		0
Number of HW-interfaces RS-232		1
Number of HW-interfaces RS-422		0
Number of HW-interfaces RS-485		1
Number of HW-interfaces serial TTY		0
Number of HW-interfaces USB		2
Number of HW-interfaces parallel		0
Number of HW-interfaces wireless		0
Number of HW-interfaces other		1
With SW interfaces		Yes
Supporting protocol for EtherCAT		No
Supporting protocol for TCP/IP		Yes
Supporting protocol for PROFIBUS		Yes
Supporting protocol for CAN		No
Supporting protocol for INTERBUS		No
Supporting protocol for ASI		No
Supporting protocol for KNX		No
Supporting protocol for Modbus		Yes
Supporting protocol for Data-Highway		No
Supporting protocol for DeviceNet		No
Supporting protocol for SUCONET		No
Supporting protocol for LON		No
Supporting protocol for PROFINET IO		No

Supporting protocol for PROFINET CBA		No
Supporting protocol for SERCOS		No
Supporting protocol for Foundation Fieldbus		No
Supporting protocol for EtherNet/IP		Yes
Supporting protocol for AS-Interface Safety at Work		No
Supporting protocol for DeviceNet Safety		No
Supporting protocol for INTERBUS-Safety		No
Supporting protocol for PROFIsafe		No
Supporting protocol for SafetyBUS p		No
Supporting protocol for other bus systems		Yes
Radio standard Bluetooth		No
Radio standard WLAN 802.11		No
Radio standard GPRS		No
Radio standard GSM		No
Radio standard UMTS		No
IO link master		No
Type of display		TFT
Colour display		Yes
Number of colours of the display		65536
Number of grey-scales/blue-scales of display		0
Screen diagonal	inch	8.4
Number of pixels, horizontal		640
Number of pixels, vertical		480
Useful project memory/user memory	kByte	64000
With numeric keyboard		Yes
With alpha numeric keyboard		Yes
Number of function buttons, programmable		0
Number of buttons with LED		0
Number of system buttons		1
Touch technology		Resistive touch
With message indication		Yes
With message system (incl. buffer and confirmation)		Yes
Process value representation (output) possible		Yes
Process default value (input) possible		Yes
With recipes		Yes
Number of password levels		200
With printer output		Yes
Number of online languages		100
Additional software components, loadable		Yes
Degree of protection (IP), front side		IP65
Degree of protection (NEMA), front side		4X
Certified for UL hazardous location class I		No
Certified for UL hazardous location class II		No
Certified for UL hazardous location class III		No
Certified for UL hazardous location division 1		No
Certified for UL hazardous location division 2		No
Certified for UL hazardous location group A (acetylene)		No
Certified for UL hazardous location group B (hydrogen)		No
Certified for UL hazardous location group C (ethylene)		No
Certified for UL hazardous location group D (propane)		No
Certified for UL hazardous location group E (metal dusts)		No
Certified for UL hazardous location group F (carbonaceous dusts)		No
Certified for UL hazardous location group G (non-conductive dusts)		No
Operating temperature	°C	0 - 50
Rail mounting possible		No

Wall mounting/direct mounting			No
Suitable for safety functions			No
Width of the front		mm	275
Height of the front		mm	208
Built-in depth		mm	47