



Undervoltage release, 12 V DC

Part no. **NZM1-XU12DC**
259450

General specifications	
Product name	Eaton Moeller series NZM release
Part no.	NZM1-XU12DC
EAN	4015082594503
Product Length/Depth	37 millimetre
Product height	66 millimetre
Product width	32 millimetre
Product weight	0.044 kilogram
Compliances	IEC UL/CSA RoHS conform
Certifications	CSA (File No. 22086) CSA-C22.2 No. 5-09 UL listed CE marking IEC60947 UL489 CSA (Class No. 1437-01) UL (File No. E140305) CSA certified UL (Category Control Number DIHS)
Product Tradename	NZM
Product Type	Accessories
Product Sub Type	Release
Delivery program	
Type	Accessory Undervoltage release
Special features	Non-delayed disconnection of NZM circuit-breaker or N switch-disconnector when the control voltage sinks below 35 – 70% US. For use with emergency-stop devices in connection with an emergency-stop button. When the under-voltage trip is switched off, accidental contact with the circuit breaker's primary contacts is prevented when switched on. Undervoltage releases cannot be installed simultaneously with NZM...-XHIV... early-make auxiliary contact or NZM...-XA... shunt release.
Frame	NZM1
Suitable for	Off-load switch
Used with	NZM1(-4), N(S)1(-4)
Technical Data - Electrical	
Voltage type	AC
Rated control voltage (relay contacts)	12 V DC
Rated control supply voltage	12 V DC
Rated control supply voltage (Us) at AC, 50 Hz - min	0 V
Rated control supply voltage (Us) at AC, 50 Hz - max	0 V
Rated control supply voltage (Us) at AC, 60 Hz - min	0 V
Rated control supply voltage (Us) at AC, 60 Hz - max	0 V
Rated control supply voltage (Us) at DC - min	12 V
Rated control supply voltage (Us) at DC - max	12 V
Voltage tolerance - min	0.85
Voltage tolerance - max	1.1
Drop-out voltage of undervoltage release AC/DC - min	0.35 x Us
Drop-out voltage of undervoltage release AC/DC - max	0.7 x Us
Power consumption	0.8 W (sealing DC) 1.5 VA (sealing AC)
Pick-up power consumption at AC (undervoltage release)	1.5 V-A
Pick-up power consumption at DC (undervoltage release)	0.8 W
Reaction time	19 ms
Minimum command time - min	10 ms

Minimum command time - max		15 ms
Electric connection type		Screw connection
Technical Data - Mechanical		
Number of contacts (change-over contacts)		0
Number of contacts (normally closed contacts)		0
Number of contacts (normally open contacts)		0
Connection type		With terminal block on the left-hand switch side
Special features		Non-delayed disconnection of NZM circuit-breaker or N switch-disconnector when the control voltage sinks below 35 – 70% US. For use with emergency-stop devices in connection with an emergency-stop button. When the under-voltage trip is switched off, accidental contact with the circuit breaker's primary contacts is prevented when switched on. Undervoltage releases cannot be installed simultaneously with NZM...-XHIV... early-make auxiliary contact or NZM...-XA... shunt release.
Technical Data - Mechanical - Terminals		
Terminal capacity (solid/flexible conductor)		0.75 mm ² - 2.5 mm ² (1x) at shunt release with ferrule 0.75 mm ² - 2.5 mm ² (2x) at shunt release with ferrule 18 - 14 AWG (1x) at shunt release 18 - 14 AWG (1x) for undervoltage releases, off-delayed 18 - 14 AWG (2x) for undervoltage releases, off-delayed 0.75 mm ² - 2.5 mm ² (2x) for undervoltage releases, off-delayed with ferrule 18 - 14 AWG (2x) at shunt release 0.75 mm ² - 2.5 mm ² (1x) for undervoltage releases, off-delayed with ferrule
Design verification as per IEC/EN 61439		
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 9.0

Low-voltage industrial components (EG000017) / Under voltage coil (EC001022)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Undervoltage trip (ecl@ss13-27-37-04-17 [AKF015018])		
Rated control supply voltage AC 50 Hz	V	0 - 0
Rated control supply voltage AC 60 Hz	V	0 - 0
Rated control supply voltage DC	V	12 - 12
Voltage type for actuating		AC
Type of electric connection		Screw connection
Number of contacts as normally open contact		0
Number of contacts as normally closed contact		0
Number of contacts as change-over contact		0
Delayed		No

Suitable for power circuit breaker			No
Suitable for off-load switch			Yes
Suitable for motor safety switch			No
Suitable for overload relay			No