

DATASHEET - NZM1-XUHIV220-250DC



Undervoltage release, 220-250VDC, +2early N/O

**Part no. NZM1-XUHIV220-250DC
259555**

General specifications		
Product name		Eaton Moeller series NZM release
Part no.		NZM1-XUHIV220-250DC
EAN		4015082595555
Product Length/Depth		37 millimetre
Product height		66 millimetre
Product width		32 millimetre
Product weight		0.056 kilogram
Compliances		RoHS conform IEC UL/CSA
Certifications		IEC60947 UL (Category Control Number DIHS) CE marking CSA certified CSA (Class No. 1437-01) CSA-C22.2 No. 5-09 CSA (File No. 22086) UL (File No. E140305) UL489 UL listed
Product Tradename		NZM
Product Type		Accessories
Product Sub Type		Release
Delivery program		
Type		Accessory Undervoltage release Undervoltage release with early-make auxiliary contact
Special features		Undervoltage release with 2 early-make auxiliary contacts, e.g., for early-make connection of undervoltage release in main switch applications, as well as for interlock and load shedding circuits. For use with emergency-stop devices in connection with an emergency-stop button. When the under-voltage trip is switched off, accidental contact with the circuit breaker's primary contacts is prevented when switched on. Early make of auxiliary contacts on switching on and off (manual operation): approx. 20 ms Undervoltage releases cannot be installed simultaneously with NZM...-XHIV... early-make auxiliary contact or NZM...-XA... shunt release.
Frame		NZM1
Fitted with:		Two early-make auxiliary contacts
Suitable for		Off-load switch
Used with		NZM1(-4), N(S)1(-4)
Technical Data - Electrical		
Voltage type		AC
Rated control voltage (relay contacts)		220 V DC 250 V DC
Rated control supply voltage		220 - 250 V DC
Rated control supply voltage (Us) at AC, 50 Hz - min		0 V
Rated control supply voltage (Us) at AC, 50 Hz - max		0 V
Rated control supply voltage (Us) at AC, 60 Hz - min		0 V
Rated control supply voltage (Us) at AC, 60 Hz - max		0 V
Rated control supply voltage (Us) at DC - min		220 V
Rated control supply voltage (Us) at DC - max		250 V
Voltage tolerance - min		0.85
Voltage tolerance - max		1.1
Drop-out voltage of undervoltage release AC/DC - min		0.35 x Us
Drop-out voltage of undervoltage release AC/DC - max		0.7 x Us
Power consumption		0.8 W (sealing DC) 1.5 VA (sealing AC)

Pick-up power consumption at AC (undervoltage release)		1.5 V-A
Pick-up power consumption at DC (undervoltage release)		0.8 W
Reaction time		19 ms
Minimum command time - min		10 ms
Minimum command time - max		15 ms
Electric connection type		Screw connection
Technical Data - Mechanical		
Number of contacts (change-over contacts)		0
Number of contacts (normally closed contacts)		0
Number of contacts (normally open contacts)		2
Connection type		With terminal block on the left-hand switch side
Special features		Undervoltage release with 2 early-make auxiliary contacts, e.g., for early-make connection of undervoltage release in main switch applications, as well as for interlock and load shedding circuits. For use with emergency-stop devices in connection with an emergency-stop button. When the under-voltage trip is switched off, accidental contact with the circuit breaker's primary contacts is prevented when switched on. Early make of auxiliary contacts on switching on and off (manual operation): approx. 20 ms Undervoltage releases cannot be installed simultaneously with NZM...-XHIV... early-make auxiliary contact or NZM...-XA... shunt release.
Technical Data - Mechanical - Terminals		
Terminal capacity (solid/flexible conductor)		0.75 mm ² - 2.5 mm ² (2x) for undervoltage releases, off-delayed with ferrule 18 - 14 AWG (2x) at shunt release 18 - 14 AWG (1x) for undervoltage releases, off-delayed 18 - 14 AWG (1x) at shunt release 0.75 mm ² - 2.5 mm ² (1x) at shunt release with ferrule 0.75 mm ² - 2.5 mm ² (2x) at shunt release with ferrule 0.75 mm ² - 2.5 mm ² (1x) for undervoltage releases, off-delayed with ferrule 18 - 14 AWG (2x) for undervoltage releases, off-delayed
Design verification as per IEC/EN 61439		
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 9.0

Low-voltage industrial components (EG000017) / Under voltage coil (EC001022)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Undervoltage trip (ecl@ss13-27-37-04-17 [AKF015018])		
Rated control supply voltage AC 50 Hz	V	0 - 0
Rated control supply voltage AC 60 Hz	V	0 - 0
Rated control supply voltage DC	V	220 - 250
Voltage type for actuating		AC

Type of electric connection			Screw connection
Number of contacts as normally open contact			2
Number of contacts as normally closed contact			0
Number of contacts as change-over contact			0
Delayed			No
Suitable for power circuit breaker			No
Suitable for off-load switch			Yes
Suitable for motor safety switch			No
Suitable for overload relay			No