



Main switch assembly kit, on the right side, red, size 1

Part no. **NZM1-XSRM-R**
266673

General specifications		
Product name		Eaton Moeller series NZM operating element
Part no.		NZM1-XSRM-R
EAN		4015082666736
Product Length/Depth		190 millimetre
Product height		180 millimetre
Product width		145 millimetre
Product weight		1.536 kilogram
Compliances		IEC UL/CSA RoHS conform
Certifications		CSA certified UL489 CSA (Class No. 1437-01) UL (Category Control Number DIHS) IEC60947 UL listed CE marking CSA (File No. 22086) CSA-C22.2 No. 5-09 UL (File No. E140305)
Product Tradename		NZM
Product Type		Accessories
Product Sub Type		Operating element
Delivery program		
Type		Accessory Main switch assembly kit for side panel mounting
Features		Lockable For direct mounting of circuit-breaker and handle in the side wall of the control cabinet Red-yellow for emergency switching off
Special features		External warning plate/designation label can be clipped on. For enhanced busbar tag shroud on the incomer side, please order IP2X protection against contact with a finger. Kit for use as a main switch
Frame		NZM1
Fitted with:		Black and yellow lightning symbol External warning plate/markings plate in German/English Special short extension shaft Door coupling rotary handle Mounting brackets Padlock
Suitable for		Power circuit breaker Switch disconnecter Emergency stop
Used with		N(S)1(-4) PN1(-4) NZM1(-4)
Technical Data - Mechanical		
Color		Red
Cover/door type		Door interlock lockable in 0 position on handle Narrowest minimum clearance between enclosure side plates of control panel and circuit breaker is defined by mounting bracket. Door interlock extension cannot be used.
Degree of protection / NEMA enclosure type		IP66 4X. 12
Activation type		Actuation on the right
Special features		External warning plate/designation label can be clipped on. For enhanced busbar tag shroud on the incomer side, please order IP2X protection against contact with a finger. Kit for use as a main switch
Design verification as per IEC/EN 61439		
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat			Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects			Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation			Meets the product standard's requirements.
10.2.5 Lifting			Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact			Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions			Meets the product standard's requirements.
10.3 Degree of protection of assemblies			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			Meets the product standard's requirements.
10.5 Protection against electric shock			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			Is the panel builder's responsibility.
10.8 Connections for external conductors			Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			Is the panel builder's responsibility.
10.10 Temperature rise			The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 9.0

Low-voltage industrial components (EG000017) / Handle for power circuit breaker (EC000229)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Handle for switch devices (ecl@ss13-27-37-04-14 [AKF012019])			
With restart blockage			No
With key lock			No
Padlock locking			Yes
Colour			Red
Suitable for emergency stop			Yes
With extension shaft			No
Suitable for power circuit breaker			Yes
Suitable for switch disconnecter			Yes
Degree of protection (NEMA)			4X, 12