



Insulated enclosure, box size HxWxD=280x200x160mm, for NZM size 2



Part no. **NZM1-XCIK5-TVD**
271521

General specifications		
Product name		Eaton xEnergy Safety Ci MCCB enclosure
Part no.		NZM1-XCIK5-TVD
EAN		4015082715212
Product Length/Depth		160 millimetre
Product height		280 millimetre
Product width		200 millimetre
Product weight		2.107 kilogram
Compliances		IEC RoHS conform
Product Tradename		xEnergy Safety Ci
Product Type		MCCB enclosure
Product Sub Type		None
Delivery program		
Type		xEnergy Safety Ci
Model		Surface mounting
Accessory/spare part type		Others
Number of poles		Three-pole
Technical Data - Electrical		
Rated uninterrupted current (Iu) at max. cross section		63 A
Technical Data - Mechanical		
Enclosure		CI-K5-160-M
Enclosure material		Plastic
Frame		NZM1
Degree of protection		Other IP65
Locking facility		Lockable on the 0 position on the handle using up to 3 padlocks. Additionally with cover interlock.
Additional information		
Fitted with:		Standard, black/gray Transparent cover
Special features		With door coupling rotary handle Complete with all required functional parts
Used with		PN1 N(S)1 xEnergy Safety Ci

Technical data ETIM 9.0

Low-voltage industrial components (EG000017) / Empty enclosure for switchgear (EC000712)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Empty housing for switch devices (ecl@ss13-27-37-13-01 [AKN343019])		
Housing material		Plastic
Width	mm	200
Height	mm	280
Depth	mm	160
With transparent cover		Yes
Suitable for emergency stop		No
Model		Surface mounting
Degree of protection (IP)		Other
Degree of protection (NEMA)		Other