

# DATASHEET - NZM1-XCI43-TVDVR



Insulated enclosure, box size HxWxD=375x250x175mm, for NZM size 2

Part no. **NZM1-XCI43-TVDVR**  
**271528**

General specifications		
Product name		Eaton xEnergy Safety Ci MCCB enclosure
Part no.		NZM1-XCI43-TVDVR
EAN		4015082715281
Product Length/Depth		175 millimetre
Product height		375 millimetre
Product width		250 millimetre
Product weight		4.103 kilogram
Compliances		RoHS conform IEC
Certifications		CE
Product Tradename		xEnergy Safety Ci
Product Type		MCCB enclosure
Product Sub Type		None
Catalog Notes		Lockable in the 0 position using up to 3 padlocks on the handle and/or switch each. Additionally with cover interlock.
Delivery program		
Type		xEnergy Safety Ci
Model		Surface mounting
Accessory/spare part type		Others
Number of poles		Three-pole/Four-pole
Technical Data - Electrical		
Rated uninterrupted current (Iu) at max. cross section		125 A
Technical Data - Mechanical		
Enclosure		CI43-150
Enclosure material		Plastic
Frame		NZM1
Degree of protection		Other IP65
Locking facility		Lockable in the 0 position using up to 3 padlocks on the handle and/or switch each. Additionally with cover interlock.
Additional information		
Fitted with:		Transparent cover Red-yellow for emergency switching off
Special features		With door coupling rotary handle Complete with all required functional parts
Suitable for		Emergency stop
Used with		xEnergy Safety Ci NZM1(-4), PN1(-4), N(S)1(-4)

## Technical data ETIM 9.0

Low-voltage industrial components (EG000017) / Empty enclosure for switchgear (EC000712)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Empty housing for switch devices (ecl@ss13-27-37-13-01 [AKN343019])		
Housing material		Plastic
Width	mm	250
Height	mm	375
Depth	mm	175
With transparent cover		Yes
Suitable for emergency stop		Yes
Model		Surface mounting
Degree of protection (IP)		IP65

