

Shaft extension



Part no. ZAV-T0
027044
EL Number 1456555
(Norway)

General specifications	
Product name	Eaton Moeller® series ZAV Accessory Shaft extension
Part no.	ZAV-T0
EAN	4015080270447
Product Length/Depth	35 millimetre
Product height	14 millimetre
Product width	35 millimetre
Product weight	0.003 kilogram
Certifications	UL/CSA certification not required
Product Tradename	ZAV
Product Type	Accessory
Product Sub Type	Shaft extension
Features & Functions	
Material	Plastic
General information	
Shaft length	25 mm
Type	Shaft extension
Climatic environmental conditions	
Ambient operating temperature - min	-25 °C
Ambient operating temperature - max	50 °C
Design verification	
Equipment heat dissipation, current-dependent Pvid	0 W
Heat dissipation capacity Pdiss	0 W
Heat dissipation per pole, current-dependent Pvid	0 W
Rated operational current for specified heat dissipation (In)	0 A
Static heat dissipation, non-current-dependent Pvs	0 W
10.2.2 Corrosion resistance	Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures	Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat	Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects	Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation	Meets the product standard's requirements.
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of assemblies	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.
10.10 Temperature rise	Not applicable.
10.11 Short-circuit rating	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility	Is the panel builder's responsibility. The specifications for the switchgear must be observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Switch operating shaft (EC000916)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Switch axle (ecl@ss10.0.1-27-37-04-13 [AKF011013])

Length	mm	25
Cross section height	mm	12
Cross section width	mm	12