


Connection terminal, 1000A, 1p, flat/round

Part no. **K3X240/1**









Catalog No. **060612**

EL-Nummer (Norway) **4132426**

### Delivery program

Product range			General switchboard accessories
Product function			Accessories panel building
Accessories			Terminations
Accessories			Terminals, 160 – 1000 A
Rated insulation voltage	U <sub>i</sub>	V AC	1000
Description			Including labels for terminal marking U, V, W - X, Y, Z - L1, L2, L3 - T1, T2, T3 - PE, N, PEN,  Relationship of rated operational current → terminal capacity to IEC/EN 60439, VDE 0660 Part 500 or EN 50021 Outer terminal for round or sectoral conductor, other side for Cu strip
Rated operational current	I <sub>e</sub>	A	1000
Pole			1

### Terminal capacity

Cu/Al cable			
			<ul style="list-style-type: none"> <li>Cu</li> <li> Round stranded</li> <li> Sectoral stranded</li> <li> Round solid</li> <li> Sectoral solid</li> <li>Al</li> <li> Round solid</li> <li> Sectoral solid</li> </ul>
			2 x 150 - 300 3 x 50 - 240
Al cable			
			<ul style="list-style-type: none"> <li>Al</li> <li> Sectoral solid</li> </ul>
			2 x 150 - 240 3 x 150 - 185
Copper band		mm	2 x (11 x 21 x 1) 10 x 40 x 1 10 x 50 x 1
conductor			# copper strip 60 x 15  Cu bar

**Notes** Conversion kits for strip terminal in cable connection available separately  
Terminal covers available separately

### Technical data ETIM 7.0

Energy distribution systems (EG000015) / Rail terminal bar (EC000275)			
Electric engineering, automation, process control engineering / Electrical insulation and connecting material / Energy distribution system / Rail terminal bar clamp (ecl@ss10.0.1-27-40-06-03 [AC0369011])			
Number of poles			1
Nominal current		A	1000
Connection type			Screwing
Mounting method			Screw
Number of connections total			2
Number of connections < 6 mm <sup>2</sup>			0
Number of connections 10 mm <sup>2</sup>			0

Number of connections 16 mm <sup>2</sup>		0
Number of connections 25 mm <sup>2</sup>		0
Number of connections > 25 mm <sup>2</sup>		2
Number of connections < AWG 6		0
Number of connections AWG 6		0
Number of connections AWG 4		0
Number of connections AWG 2		0
Number of connections AWG 4/0		0
Number of connections 250 kcmil		0
Number of connections > 250 kcmil		0
Contact safe		Yes
Height	mm	196
Width	mm	88
Depth	mm	165