

ON-OFF switches, TM, 10 A, flush mounting, 2 contact unit(s), Contacts: 3, 90 °, maintained, With 0 (Off) position, 0-1, Design number 8292



Powering Business Worldwide™

**Part no. TM-2-8292/E
074877**

General specifications	
Product name	Eaton Moeller® series TM On-Off switch
Part no.	TM-2-8292/E
EAN	4015080748779
Product Length/Depth	74 millimetre
Product height	30 millimetre
Product width	43 millimetre
Product weight	0.037 kilogram
Certifications	CSA-C22.2 No. 94 UL 508 Certified by UL for use in Canada UL CSA-C22.2 No. 14-05 IEC/EN 60947 CSA IEC/EN 60947-3 IEC/EN 60947-5-1 VDE 0660 UL Category Control No.: NLRV UL report applies to both US and Canada UL File No.: E36332 CE
Product Tradename	TM
Product Type	On-Off switch
Product Sub Type	None
Features & Functions	
Fitted with:	Black thumb grip and front plate
Inscription	0-1
Number of poles	3
General information	
Degree of protection	NEMA 12
Degree of protection (front side)	IP65
Lifespan, mechanical	1,000,000 Operations
Mounting method	Flush mounting
Mounting position	As required
Number of contact units	2
Operating frequency	1200 Operations/h
Overvoltage category	III
Pollution degree	3
Rated impulse withstand voltage (Uimp)	4000 V AC
Suitable for	Front mounting 4-hole
Switching angle	90 °
Type	ON-OFF switch
Climatic environmental conditions	
Ambient operating temperature - min	-25 °C
Ambient operating temperature - max	50 °C
Climatic proofing	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
Terminal capacities	
Terminal capacity	2 x 1.0 mm ² , flexible with ferrules to DIN 46228 1 x 1.5 mm ² , flexible 1 x 1.5 mm ² , solid or stranded 2 x 1.5 mm ² , flexible 14 AWG, solid or flexible with ferrule 2 x 1.5 mm ² , solid or stranded

		1 x 1.0 mm ² , flexible with ferrules to DIN 46228
Screw size		M2.5, Terminal screw
Tightening torque		3.5 lb-in, Screw terminals 0.4 Nm, Screw terminals
Electrical rating		
Rated operational current (I _e) at AC-21, 440 V		10 A
Rated operational power at AC-3, 380/400 V, 50 Hz		0 kW
Rated operational power at AC-23A, 400 V, 50 Hz		3 kW
Rated uninterrupted current (I _u)		10 A
Uninterrupted current		Rated uninterrupted current I _u is specified for max. cross-section.
Short-circuit rating		
Rated conditional short-circuit current (I _q)		0 kA
Rated short-time withstand current (I _{cw})		0 kA
Short-circuit protection rating		10 A gG/gL, Fuse, Contacts
Switching capacity		
Switching capacity (main contacts, general use)		10 A, Rated uninterrupted current max. (UL/CSA)
Switching capacity (auxiliary contacts, general use)		10A, IU, (UL/CSA)
Switching capacity (auxiliary contacts, pilot duty)		A300 (UL/CSA)
Motor rating		
Assigned motor power at 115/120 V, 60 Hz, 1-phase		0.33 HP
Assigned motor power at 115/120 V, 60 Hz, 3-phase		0.75 HP
Assigned motor power at 230/240 V, 60 Hz, 1-phase		0.75 HP
Assigned motor power at 230/240 V, 60 Hz, 3-phase		1 HP
Assigned motor power at 277 V, 60 Hz, 1-phase		0.75 HP
Contacts		
Control circuit reliability		1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
Number of auxiliary contacts (change-over contacts)		0
Number of auxiliary contacts (normally closed contacts)		0
Number of auxiliary contacts (normally open contacts)		0
Actuator		
Actuator color		Black
Actuator function		Maintained With 0 (Off) position
Actuator type		Short thumb-grip
Design verification		
Equipment heat dissipation, current-dependent P _{vid}		0 W
Heat dissipation capacity P _{diss}		0 W
Heat dissipation per pole, current-dependent P _{vid}		0.15 W
Rated operational current for specified heat dissipation (I _n)		10 A
Static heat dissipation, non-current-dependent P _{vs}		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		UV resistance only in connection with protective shield.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Switch disconnecter (EC000216)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Switch disconnecter (ecl@ss10.0.1-27-37-14-03 [AKF060013])		
Version as main switch		No
Version as maintenance-/service switch		No
Version as safety switch		No
Version as emergency stop installation		No
Version as reversing switch		No
Number of switches		1
Max. rated operation voltage Ue AC	V	500
Rated operating voltage	V	500 - 500
Rated permanent current Iu	A	10
Rated permanent current at AC-23, 400 V	A	
Rated permanent current at AC-21, 400 V	A	0
Rated operation power at AC-3, 400 V	kW	0
Rated short-time withstand current Icw	kA	0
Rated operation power at AC-23, 400 V	kW	3
Switching power at 400 V	kW	0
Conditioned rated short-circuit current Iq	kA	0
Number of poles		3
Number of auxiliary contacts as normally closed contact		0
Number of auxiliary contacts as normally open contact		0
Number of auxiliary contacts as change-over contact		0
Motor drive optional		No
Motor drive integrated		No
Voltage release optional		No
Device construction		Built-in device fixed built-in technique
Suitable for floor mounting		No
Suitable for front mounting 4-hole		Yes
Suitable for front mounting centre		No
Suitable for distribution board installation		No
Suitable for intermediate mounting		No
Colour control element		Black
Type of control element		Short thumb-grip
Interlockable		No
Type of electrical connection of main circuit		Screw connection
Degree of protection (IP), front side		IP65
Degree of protection (NEMA)		12