





Standard auxiliary contact, NHI-E, 1 N/O, Can be fitted to the front, Screw terminals

Part no. **NHI-E-10-PKZ0**
 Catalog No. **082884**
 Alternate Catalog No. **XTPAXFA10**
 No.
 EL-Nummer **4315150**
 (Norway)

Delivery program

| | | |
|---|--|---|
| Product range | | Accessories |
| Accessories | | Standard auxiliary contact |
| | | Can be fitted to the front Terminal designation differs to that of an auxiliary contact that can be fitted to the side |
| Contacts | | |
| N/O = Normally open | | 1 N/O |
| Contact diagram | |  |
| Contact sequence | |  |
| Connection technique | | Screw terminals |
| For use with | | PKZ0(4) standard auxiliary contacts |
| For use with | | DILM |
| Notes Can be fitted to: Motor protective circuit-breaker Transformer-protective circuit-breaker Motor protective circuit breaker for starter combinations (From serial number 01) 45 mm (PKZM0 and PKZM01) or 55 mm (PKZM4) widths of the motor-protective circuit-breakers remain unchanged. | | |

Technical data

Auxiliary contacts

| | | | | |
|---------------------------------------|--|------------|---|-------|
| Rated impulse withstand voltage | U_{imp} | V AC | 4000 | |
| Overvoltage category/pollution degree | | | III/3 | |
| Rated operational voltage | U_e | V | | |
| | U_e | V AC | 440 | |
| | U_e | V DC | 250 | |
| Safe isolation to EN 61140 | | | | |
| | Between auxiliary contacts and main contacts | V AC | 690 | |
| Rated operational current | I_e | A | | |
| | AC-15 | | | |
| | 220 - 240 V | I_e | A | 1 |
| | DC-13 L/R - 100 ms | | | |
| 24 V | I_e | A | 2 | |
| Lifespan | | S | | |
| | Lifespan, mechanical | Operations | $\times 10^6$ | > 0.1 |
| | Lifespan, electrical | Operations | $\times 10^6$ | 0.1 |
| Control circuit reliability | Failure rate | λ | $< 10^{-8}$, < one failure at 100 million operations (at $U_e = 24$ V DC, $U_{min} = 17$ V, $I_{min} = 5.4$ mA) | |

| | | | |
|--------------------------------------|---------|----|--|
| Short-circuit rating without welding | | | |
| Fuse | A gG/gL | 10 | |

Terminal capacities

| | | | |
|---|-----------------|------------|--|
| Solid or flexible conductor, with ferrule | mm ² | 0,75 - 1,5 | |
| Solid or stranded | AWG | 18 - 16 | |

Rating data for approved types

| | | | |
|-------------|---|-----|------|
| Pilot Duty | | | |
| AC operated | | | E150 |
| General Use | | | |
| DC | V | 250 | |
| DC | A | 0.5 | |

Design verification as per IEC/EN 61439

| | | | |
|--|-------------------|----|--|
| Technical data for design verification | | | |
| Rated operational current for specified heat dissipation | I _n | A | 1 |
| Heat dissipation per pole, current-dependent | P _{vid} | W | 0.01 |
| Equipment heat dissipation, current-dependent | P _{vid} | W | 0 |
| Static heat dissipation, non-current-dependent | P _{vs} | W | 0 |
| Heat dissipation capacity | P _{diss} | W | 0 |
| Operating ambient temperature min. | | °C | -25 |
| Operating ambient temperature max. | | °C | 55 |
| IEC/EN 61439 design verification | | | |
| 10.2 Strength of materials and parts | | | |
| 10.2.2 Corrosion resistance | | | Meets the product standard's requirements. |
| 10.2.3.1 Verification of thermal stability of enclosures | | | Meets the product standard's requirements. |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat | | | Meets the product standard's requirements. |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects | | | Meets the product standard's requirements. |
| 10.2.4 Resistance to ultra-violet (UV) radiation | | | Meets the product standard's requirements. |
| 10.2.5 Lifting | | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.6 Mechanical impact | | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.7 Inscriptions | | | Meets the product standard's requirements. |
| 10.3 Degree of protection of ASSEMBLIES | | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 Clearances and creepage distances | | | Meets the product standard's requirements. |
| 10.5 Protection against electric shock | | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 Incorporation of switching devices and components | | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 Internal electrical circuits and connections | | | Is the panel builder's responsibility. |
| 10.8 Connections for external conductors | | | Is the panel builder's responsibility. |
| 10.9 Insulation properties | | | |
| 10.9.2 Power-frequency electric strength | | | Is the panel builder's responsibility. |
| 10.9.3 Impulse withstand voltage | | | Is the panel builder's responsibility. |
| 10.9.4 Testing of enclosures made of insulating material | | | Is the panel builder's responsibility. |
| 10.10 Temperature rise | | | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating | | | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.12 Electromagnetic compatibility | | | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.13 Mechanical function | | | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed. |

Technical data ETIM 7.0


| | | | |
|---|--|--|---|
| Low-voltage industrial components (EG000017) / Auxiliary contact block (EC000041) | | | |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Auxiliary switch block (ec@ss10.0.1-27-37-13-02 [AKN342013]) | | | |
| Number of contacts as change-over contact | | | 0 |
| Number of contacts as normally open contact | | | 1 |
| Number of contacts as normally closed contact | | | 0 |

| | | |
|--|---|------------------|
| Number of fault-signal switches | | 0 |
| Rated operation current I _e at AC-15, 230 V | A | 1 |
| Type of electric connection | | Screw connection |
| Model | | Top mounting |
| Mounting method | | Front fastening |
| Lamp holder | | None |


Approvals

| | | |
|--------------------------------------|--|--|
| Product Standards | | UL 508; CSA-C22.2 No. 14; IEC60947-4-1; CE marking |
| UL File No. | | E36332 |
| UL Category Control No. | | NLRV |
| CSA File No. | | 165628 |
| CSA Class No. | | 3211-05 |
| North America Certification | | UL listed, CSA certified |
| Specially designed for North America | | No |


Characteristics



Dimensions



PKZM0-...(+NHI-E-...-PKZ0)
PKZM0-...-T(+NHI-E-...-PKZ0)
PKM0-...(+NHI-E-...-PKZ0)



Additional product information (links)

Motor starters and "Special Purpose Ratings" for the North American market

http://www.eaton.eu/ecm/groups/public/@pub/@europe/@electrical/documents/content/pct_3258146.pdf

Busbar Component Adapters for modern Industrial control panels

http://www.moeller.net/binary/ver_techpapers/ver960en.pdf