



Flange, knockout, 6x M20, 4x M25, 4x M25/16, HxWxD=116x250x23mm

**Part no.** FL3-2  
**Catalog No.** 090798

**EL-Nummer (Norway)** 4132117


**Delivery program**

|                                   |  |  |   |
|-----------------------------------|--|--|---|
|                                   |  |  |   |
| Product range                     |  |  | xEnergy Safety Ci   |
| Basic function                    |  |  | Basic enclosures  |
| Product function                  |  |  | Accessories for basic enclosures  |
| Accessories                       |  |  | Flanges   |
| Single unit/Complete unit         |  |  | Modular system  |
| Description                       |  |  | sponge-rubber, captive gasket<br>Quick mounting using wedge-lock fasteners (included as standard) |
| For use with enclosure dimensions |  |  | 250 mm  |
| Cable entry                       |  |  | 6 x M20, 4 x M25, 4 x M25/16  |

**Technical data ETIM 7.0**

|  |  |    |                   |
|--|--|----|-------------------|
| Distribution boards (EG000023) / Gland plate for small distribution boards/switchgear cabinets (EC000211)  |  |    |                   |
| Electric engineering, automation, process control engineering / Electrical installation, device / Electrical distribution system (incl. small distribution board) / Gland plate for small distribution boards/switchgear cabinets (ecl@ss10.0.1-27-14-24-21 [ADI315007]) |  |    |                   |
| Model  |  |    | Cable screw gland |
| Type   |  |    | Straight          |
| Width  |  | mm | 204               |
| Height   |  | mm | 116               |
| Depth  |  | mm | 23                |
| Material   |  |    | Plastic           |
| Surface protection   |  |    | Untreated         |
| Degree of protection (NEMA)  |  |    | Other             |
| Pre-stamping   |  |    | Yes               |
| Number of connector holes  |  |    | 0                 |
| Thread type  |  |    | Metric            |
| Suitable for nominal thread metric/PG  |  |    | 16 - 25           |

## Dimensions



## Additional product information (links)

|   |   |
|---|---|
| allowInterrupt=1&RevisionSelectionMethod=LatestReleased&noSaveAs=0&Renderit | <a href="http://www.eaton.eu/DE/ecm/idcplg?IdcService=GET_FILE&amp;model%20certification%20xEnergy%20Safety%20Ci">http://www.eaton.eu/DE/ecm/idcplg?IdcService=GET_FILE&amp;model certification xEnergy Safety Ci</a>                                   |
| allowInterrupt=1&RevisionSelectionMethod=LatestReleased&noSaveAs=0&Renderit | <a href="http://www.eaton.eu/DE/ecm/idcplg?IdcService=GET_FILE&amp;Save%20time%20-%20we%20assist%20you%20with%20expert%20pre-assembly">http://www.eaton.eu/DE/ecm/idcplg?IdcService=GET_FILE&amp;Save time – we assist you with expert pre-assembly</a> |
| allowInterrupt=1&RevisionSelectionMethod=LatestReleased&noSaveAs=0&Renderit | <a href="http://www.eaton.eu/DE/ecm/idcplg?IdcService=GET_FILE&amp;product%20information%20xEnergy%20Safety%20Ci">http://www.eaton.eu/DE/ecm/idcplg?IdcService=GET_FILE&amp;product information xEnergy Safety Ci</a>                                   |
| tool for calculating the power loss for switching device combinations       | <a href="http://www.eaton.eu/DE/Europe/Electrical/CustomerSupport/ConfigurationTools/TCTool/index.htm">http://www.eaton.eu/DE/Europe/Electrical/CustomerSupport/ConfigurationTools/TCTool/index.htm</a>   |
| configurator - xEnergy family   | <a href="http://www.eaton.eu/DE/Europe/Electrical/CustomerSupport/ConfigurationTools/xEnergyMainSupport/index.htm">http://www.eaton.eu/DE/Europe/Electrical/CustomerSupport/ConfigurationTools/xEnergyMainSupport/index.htm</a>                         |