



Busbar support, 3p, for flat busbars

Part no. **BBS-3/FL-NA**
107067
EL Number **2465001**
(Norway)

General specifications	
Product name	Eaton xEffect SASY 60i Enclosures Switch- & Controlgear Enclosure
Part no.	BBS-3/FL-NA
EAN	4015081069200
Product Length/Depth	50 millimetre
Product height	190 millimetre
Product width	20 millimetre
Product weight	0.149 kilogram
Compliances	IEC 60439-1 CSA-C22.2 No. 14 UL508A CE marking UL CSA09 (refer to approbation report) RoHS conform
Certifications	North America (UL listed, CSA certified) Specially designed for North America CSA (File No. 236217) UL (Category Control Number NMTR, NMTR7) UL (File No. E300273) CSA (Class No. 3211-37)
Product Tradename	xEffect SASY 60i
Product Type	Enclosures
Product Sub Type	Switch- & Controlgear Enclosure
Delivery program	
Type	60 mm system System for flat busbar
Color	Light gray (RAL 7035)
Number of poles	Three-pole
Technical Data - Electrical	
Voltage rating (UL CSA 13)	Max. 600 V AC
Current rating - max	630 A
Rated operation current (Ie)	630 A
Creepage resistance	CTI 200
Technical Data - Mechanical	
Material	Thermoplast, silicon free, chlorine free Halogen free
Degree of protection	Feeder circuits
Busbar distance	60 mm
Design verification as per IEC/EN 61439 - technical data	
Temperature resistance	Up to 120 °C
Ambient operating temperature - max	35 °C
Additional information	
Features	Halogen free Self-extinguishing acc. UL 94
Functions	Busbar support UL busbar support Current limiting circuit breaker, refer to approbation report
Special features	Can be fitted to all busbar sizes using concertina system With screw block inside
Suitable for	Three-pole
Used with	30 x 5/10 mm 12 x 5/10 mm Feeder circuits 20 x 5/10 mm System for flat busbar 60 mm system

Technical data ETIM 9.0

Energy distribution systems (EG000015) / Busbar support (EC001166)			
Electric engineering, automation, process control engineering / Electrical insulation and connecting material / Energy distribution system / Busbar carrier (ec@ss13-27-40-06-07 [AC0377016])			
Number of poles			3
Max. rated current		A	630
Busbar distance		mm	60