



Fuse-link, high speed, 10 A, AC 690 V, DC 500 V, 200 kA, BS88, 9 x 75 mm, aR, BS

Part no. **10AMP 690V AC BS88 FUSE**  
 Catalog No. **10CT**

### Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	10
Rated voltage			AC 690 V DC 500 V
Construction size			BS88
Size			9 x 75 mm
Utilization category			aR
Breaking Capacity		kA	200
usable for size/applications			DC common bus, DC drives, power converters/rectifiers and reduced voltage starters
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS88-4 IEC 60269-4

### Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / HRC fuse (EC004556)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Safety fuse inserts (unspecified) (ecl@ss10.0.1-27-14-20-90 [BAB264011])			
Fuse construction type according to IEC 60269			Other
Type of current			AC/DC
Rated voltage AC		V	690
Rated voltage DC		V	500
Rated current		A	10
Utilization category			aR (accompanied semiconductor protection)
Breaking capacity		kA	90
Colour code			None
Type of fuse status indicator			None
Power loss at rated current		W	3
Mounting holes			Other
Centre-to-centre distance of connections		mm	37.5