



Fuse switch disconnecter, 4p, NH2, AC23

Part no. PIFT2H400
Catalog No. 161213
Alternate Catalog No. PIFT2H400

Technical data ETIM 8.0

| | | |
|---|----|---------------------|
| Low-voltage industrial components (EG000017) / Fuse switch disconnecter (EC001040) | | |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Fuse switch disconnecter (ec@ss10.0.1-27-37-14-01 [AKF058013]) | | |
| Version as main switch | | No |
| Version as safety switch | | No |
| Max. rated operation voltage Ue AC | V | 690 |
| Rated permanent current Iu | A | 400 |
| Rated operation power at AC-23, 400 V | kW | 0 |
| Conditioned rated short-circuit current Iq | kA | 100 |
| Rated short-time withstand current Icw | kA | 0 |
| Suitable for fuses | | NH2 |
| Number of poles | | 4 |
| With error protection | | Yes |
| Type of electrical connection of main circuit | | Screw connection |
| Cable entry | | Side |
| Equipped with connectors | | Yes |
| Suitable for floor mounting | | No |
| Suitable for front mounting | | Yes |
| Suitable for busbar mounting | | Yes |
| Type of control element | | Long turning handle |
| Position control element | | Front side |
| Motor drive optional | | Yes |
| Motor drive integrated | | No |
| Version as emergency stop installation | | No |
| Degree of protection (IP), front side | | IP40 |

Additional product information (links)

| | |
|--------------------------|---|
| Instruction leaflet PIFT | https://es-assets.eaton.com/ENGINEERING/CONFIGURATOR/XENERGY/IL-PIFT-01M-2018-08.pdf |
|--------------------------|---|