



Miniature circuit breaker (MCB), 40 A, 3p, characteristic: C

Part no. **FAZT-C40/3**
142496
EL Number **1605534**
(Norway)

| General specifications | |
|---|--|
| Product name | Eaton Moeller series xEffect - FAZ-T MCB |
| Part no. | FAZT-C40/3 |
| EAN | 4015081392261 |
| Product Length/Depth | 80 millimetre |
| Product height | 75.5 millimetre |
| Product width | 54 millimetre |
| Product weight | 0.362 kilogram |
| Compliances | RoHS conform |
| Certifications | IEC/EN 60947-2 EN45545-2 IEC 61373 |
| Product Tradename | xEffect - FAZ-T |
| Product Type | MCB |
| Product Sub Type | None |
| Delivery program | |
| Application | Switchgear for industrial and advanced commercial applications xEffect - Switchgear for industrial and advanced commercial applications |
| Number of poles | Three-pole |
| Number of poles (total) | 3 |
| Number of poles (protected) | 3 |
| Tripping characteristic | C |
| Release characteristic | C |
| Amperage Rating | 40 A |
| Type | FAZ-T Miniature circuit breaker |
| Technical Data - Electrical | |
| Voltage type | AC |
| Voltage rating (IEC/EN 60898-1) | 400 V AC |
| Voltage rating (IEC/EN 60947-2) | 415 V |
| Rated operational voltage (Ue) - max | 440 V |
| Operational voltage (IEC/EN 60947-2) - max | 440 V AC |
| Operational voltage at DC (IEC/EN 60947-2) - max | 60 V DC |
| Rated insulation voltage (Ui) | 440 V |
| Rated impulse withstand voltage (Uimp) | 4 kV |
| Frequency rating | 50 Hz / 60 Hz |
| Frequency rating - min | 50 Hz |
| Frequency rating - max | 60 Hz |
| Rated switching capacity (IEC/EN 60947-2) at max voltage rating | 15 kA |
| Rated switching capacity (IEC/EN 60947-2) | 20 kA |
| Rated switching capacity (IEC/EN 60898-1) | 10 kA |
| Rated service short-circuit breaking capacity (IEC/EN 60898-1) | 7.5 kA |
| Rated service short-circuit breaking capacity (IEC/EN 60947-2) | 7.5 kA |
| Rated short-circuit breaking capacity (EN 60898) at 230 V | 15 kA |
| Rated short-circuit breaking capacity (EN 60898) at 400 V | 15 kA |
| Rated short-circuit breaking capacity (IEC 60947-2) at 230 V | 15 kA |
| Rated short-circuit breaking capacity (IEC 60947-2) at 400 V | 15 kA |
| Lifespan, electrical | 4000 operations |
| Overvoltage category | III |

| | | |
|--|--|--|
| Pollution degree | | 2 |
| Direction of incoming supply | | As required |
| Technical Data - Mechanical | | |
| Frame | | 45 mm |
| Enclosure width | | 80 mm |
| Width in number of modular spacings | | 3 |
| Built-in depth | | 70.5 mm |
| Mounting width | | 17.5 mm |
| Mounting width per pole | | 17.5 mm |
| Mounting Method | | Quick attachment with 3 latch positions for top-hat rail IEC/EN 60715 |
| Mounting position | | As required |
| Degree of protection | | IP20 |
| Terminal capacity | | 1 mm ² - 25 mm ² |
| Terminals (top and bottom) | | Twin-purpose terminals |
| Connectable conductor cross section (solid-core) - min | | 1 mm ² |
| Connectable conductor cross section (solid-core) - max | | 25 mm ² |
| Connectable conductor cross section (multi-wired) - min | | 1 mm ² |
| Connectable conductor cross section (multi-wired) - max | | 25 mm ² |
| Terminal protection | | Finger and hand touch safe, DGUV VS3, EN 50274 |
| Tightening torque | | Max. 2.4 Nm |
| Busbar material thickness | | 0.8 mm (except N 0.5 SU) |
| Lifespan, mechanical | | 10000 operations |
| Design verification as per IEC/EN 61439 - technical data | | |
| Rated operational current for specified heat dissipation (In) | | 40 A |
| Heat dissipation per pole, current-dependent | | 0 W |
| Equipment heat dissipation, current-dependent | | 11.2 W |
| Static heat dissipation, non-current-dependent | | 0 W |
| Heat dissipation capacity | | 0 W |
| Ambient operating temperature - min | | -25 °C |
| Ambient operating temperature - max | | 75 °C |
| Design verification as per IEC/EN 61439 | | |
| 10.2.2 Corrosion resistance | | Meets the product standard's requirements. |
| 10.2.3.1 Verification of thermal stability of enclosures | | Meets the product standard's requirements. |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat | | Meets the product standard's requirements. |
| 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects | | Meets the product standard's requirements. |
| 10.2.4 Resistance to ultra-violet (UV) radiation | | Meets the product standard's requirements. |
| 10.2.5 Lifting | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.6 Mechanical impact | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.7 Inscriptions | | Meets the product standard's requirements. |
| 10.3 Degree of protection of assemblies | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 Clearances and creepage distances | | Meets the product standard's requirements. |
| 10.5 Protection against electric shock | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 Incorporation of switching devices and components | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 Internal electrical circuits and connections | | Is the panel builder's responsibility. |
| 10.8 Connections for external conductors | | Is the panel builder's responsibility. |
| 10.9.2 Power-frequency electric strength | | Is the panel builder's responsibility. |
| 10.9.3 Impulse withstand voltage | | Is the panel builder's responsibility. |
| 10.9.4 Testing of enclosures made of insulating material | | Is the panel builder's responsibility. |
| 10.10 Temperature rise | | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating | | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.12 Electromagnetic compatibility | | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.13 Mechanical function | | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed. |

| Additional information | | |
|------------------------|--|---|
| Current limiting class | | 3 |
| Features | | Additional equipment possible |
| Special features | | Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity |
| Used with | | FAZ-T Miniature circuit breaker |

Technical data ETIM 9.0

| Circuit breakers and fuses (EG000020) / Miniature circuit breaker (MCB) (EC000042) | | |
|---|-----------------|----------|
| Electric engineering, automation, process control engineering / Electrical installation, device / Miniature circuit breaker system (MCB) / Miniature circuit breaker (MCB) (ecl@ss13-27-14-19-01 [AAB905019]) | | |
| Built-in depth | mm | 70.5 |
| Release characteristic | | C |
| Number of poles (total) | | 3 |
| Number of protected poles | | 3 |
| Rated current | A | 40 |
| Rated voltage | V | 440 |
| Rated insulation voltage Ui | V | 440 |
| Rated impulse withstand voltage Uimp | kV | 4 |
| Rated short-circuit breaking capacity Icn according to EN 60898 at 230 V | kA | 15 |
| Voltage type | | AC |
| Rated short-circuit breaking capacity Icn according to EN 60898 at 400 V | kA | 15 |
| Rated short-circuit breaking capacity Icu according to IEC 60947-2 at 230 V | kA | 15 |
| Rated short-circuit breaking capacity Icu according to IEC 60947-2 at 400 V | kA | 15 |
| Frequency | Hz | 50 - 60 |
| Power loss | W | 11.2 |
| Current limiting class | | 3 |
| Flush-mounted installation | | No |
| Concurrently switching neutral conductor | | No |
| Over voltage category | | 3 |
| Pollution degree | | 2 |
| Additional equipment possible | | Yes |
| Width in number of modular spacings | | 3 |
| Degree of protection (IP) | | IP20 |
| Ambient temperature during operating | °C | -25 - 75 |
| Connectable conductor cross section multi-wired | mm ² | 1 - 25 |
| Connectable conductor cross section solid-core | mm ² | 1 - 25 |
| Explosion-proof | | No |