

Tipo PIFT1L331C251CCA
Catalog No. 158790
Alternate Catalog No. PIFT1L331C251CCA

Abbildung ähnlich

Dati tecnici secondo ETIM 6.0

| | | | |
|---|----|--|----------------------------|
| Low-voltage industrial components (EG000017) / Fuse switch disconnecter (EC001040) | | | |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Fuse switch disconnecter (ecl@ss8.1-27-37-14-01 [AKF058010]) | | | |
| Version as main switch | | | No |
| Version as safety switch | | | No |
| Max. rated operation voltage Ue AC | V | | 690 |
| Rated permanent current Iu | A | | 250 |
| Rated operation power at AC-23, 400 V | kW | | 0 |
| Conditioned rated short-circuit current Iq | kA | | 55 |
| Rated short-time withstand current Icw | kA | | 0 |
| Suitable for fuses | | | NH1 |
| Number of poles | | | 3 |
| With error protection | | | No |
| Type of electrical connection of main circuit | | | Screw connection |
| Suitable for ground mounting | | | No |
| Suitable for front mounting 4-hole | | | No |
| Suitable for busbar mounting | | | Yes |
| Type of control element | | | Door coupling rotary drive |
| Position control element | | | Front side |
| Motor drive optional | | | No |
| Motor drive integrated | | | No |
| Version as emergency stop installation | | | No |
| Degree of protection (IP), front side | | | IP40 |

Ulteriori informazioni sul prodotto (link)

| | |
|-----------------------------|---|
| Libretto di istruzioni PIFT | https://es-assets.eaton.com/ENGINEERING/CONFIGURATOR/XENERGY/IL/IL-PIFT-01M-2018-08.pdf |
|-----------------------------|---|