




Phase monitoring relays, On- and Off-delayed, 300 - 500 V AC, 50/60 Hz

Part no. **EMR6-W500-D-1**  
 Catalog No. **184779**  
 Alternate Catalog No. **EMR6-W500-D-1**  
 EL-Nummer (Norway) **4101975**

**Delivery program**

Product range			EMR Measuring and monitoring relays
Basic function			Phase monitoring relays
Function			On- and Off-delayed
			Power supply from the measuring circuit On-delay/off-delay: none = 0 or adjustable between 0.1 - 30 s Imbalance threshold values adjustable 2 - 25 % of mean value of phase voltages Three-phase networks
Monitoring voltage per phase	$U_N$	V AC	300 - 500 V AC, 50/60 Hz
Monitoring of			Phase sequence (can be deactivated) Phase failure Overvoltage Undervoltage
Contact sequence			
Supply voltage			300 - 500 V AC, 50/60 Hz
Width		mm	22.5

**Technical data**

<b>General</b>			
Standards			IEC, UL, CSA, CCC, GL
Lifespan, mechanical	Operations	$\times 10^6$	30
Climatic proofing			Damp heat, cyclical to IEC 60068-2-30: 24 h cycle, 55° C, 93% relative humidity, 96 h
Ambient temperature			
Operation		°C	
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	+ 60
Storage		°C	- 40 - 85
Mounting position			As required
Shock resistance			Class 2
Degree of protection			
Terminals			IP20
Enclosures			IP50
Terminal capacities		mm <sup>2</sup>	
Solid		mm <sup>2</sup>	1 x 0.5-2.5 (1 x 18-14 AWG)
Flexible with ferrule		mm <sup>2</sup>	2 x 0.5-1.5 (2 x 18-16 AWG)
Standard screwdriver		mm	5.5 x 0.8
Tightening torque		Nm	0.6 - 0.8
Fixing			Snap fixing, top-hat rail IEC/EN 60715
MTBF (mean time between failures)			382977 h

**Contacts**

Rated impulse withstand voltage	$U_{imp}$	V AC	4000
Overvoltage category/pollution degree			III/3

**Power supply**

Supply voltage			300 - 500 V AC, 50/60 Hz
----------------	--	--	--------------------------

Voltage tolerance		x U <sub>c</sub>	0.85 - 1.1
Power consumption		VA	18
Rated frequency	f	Hz	50 - 60
Duty factor		% DF	100

### Timing cycle

Response delay time		s	0.2
Reset delay/Off-delay time		s	Adjustable from 0.1 – 30
Time error within supply voltage		%	0.5
Time error within temperature range		%/°C	0.06

### Measuring circuits

Frequency		Hz	50/60 ± 10 %
Hysteresis		%	0 ... 5
Frequency		Hz	50/60 ± 10 %
Measuring cycle		ms	50
Temperature error		%/°C	0.06
Error within supply voltage		%	0.5

### Status indication

Supply voltage			LED yellow
Overvoltage			LED red: F1 on
Undervoltage			LED red: F2 on
Status indicator (LED)			Yellow, solid: Supply voltage Yellow, solid (R/T): Relay energized Yellow, flashing (R/T): Delay time running Red, solid (F1): Overvoltage Red, solid (F2): Undervoltage Red: F1 solid, F2 flashing: Phase failure Red, flashing (F1 & F2 alternating): Phase sequence fault

### Relay output contacts

Rated operational voltage	U <sub>e</sub>	V AC	250
Rated operational current	I <sub>e</sub>	A	
AC-12 at 230 V	I <sub>e</sub>	A	4
AC-15 with 230 V	I <sub>e</sub>	A	3
DC-12 at 24 V	I <sub>e</sub>	A	4
DC-13 at 24 V	I <sub>e</sub>	A	2
Minimum Switching capacity			10 mA / 24 V
Lifespan, electrical (AC-12/230 V/4 A)	Operations	x 10 <sup>6</sup>	
Lifespan, electrical	Operations	x 10 <sup>6</sup>	0.1
Short-circuit rating			
max. fuse	Fast/gL	A	5

### Electromagnetic compatibility (EMC)

Electromagnetic compatibility			IEC/EN 60947-6-2
ESD	Air/contact discharge	kV	IEC/EN 61000-4-2 level 3
HF-immunity to radiation			IEC/EN 61000-4-3 level 3
Burst			IEC/EN 61000-4-4 level 3
Surge			IEC/EN 61000-4-5 Level 4
HF-immunity to line-conducted interference			IEC/EN 61000-4-6 level 3

### Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	60

### Technical data ETIM 8.0


Relays (EG000019) / Phase monitoring relay (EC001441)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Monitoring equipment (low-voltage switch technology) / Asymmetry monitoring equipment (ecI@ss10.0.1-27-37-18-03 [AKF097014])			
Type of electric connection			Screw connection
With detachable clamps			No

Rated control supply voltage Us at AC 50HZ	V	300 - 500
Rated control supply voltage Us at AC 60HZ	V	300 - 500
Rated control supply voltage Us at DC	V	0 - 0
Voltage type for actuating		AC
Phase sequence monitoring		Yes
Phase failure detection		Yes
Function under voltage detection		Yes
Function over voltage detection		Yes
Phase imbalance monitoring		No
Voltage measuring range	V	300 - 500
Min. adjustable delay-on energization time	s	0.1
Max. permitted delay-on energization time	s	30
Min. adjustable off-delay time	s	0.1
Max. permitted off-delay time	s	30
Number of contacts as normally closed contact		0
Number of contacts as normally open contact		0
Number of contacts as change-over contact		2
Width	mm	22.5
Height	mm	85.6
Depth	mm	103.7

## Approvals

Product Standards		IEC 255-6; UL 508; CSA-22.2 No. 14-05; CE marking
UL File No.		E29184
UL Category Control No.		NKCR, NKCR7
CSA File No.		UL report valid
CSA Class No.		3211-03
North America Certification		UL listed, certified by UL for use in Canada

## Dimensions



## Additional product information (links)

<b>IL121006ZU Single-function three-phase monitoring relays</b>	
IL121006ZU Single-function three-phase monitoring relays	<a href="https://es-assets.eaton.com/DOCUMENTATION/AWA_INSTRUCTIONS/IL121006ZU.pdf">https://es-assets.eaton.com/DOCUMENTATION/AWA_INSTRUCTIONS/IL121006ZU.pdf</a>
Phase monitoring relays	<a href="http://ecat.moeller.net/flip-cat/?edition=HPLEN&amp;startpage=11.36">http://ecat.moeller.net/flip-cat/?edition=HPLEN&amp;startpage=11.36</a>