



EV busbars 1Ph., 6HP, 63A for PLS. CLS. PKN., PFIM, PFHM, PFNM

Part no. EVG-1PHAS/6MODUL
Catalog No. 215638

Similar to illustration

Delivery program

Basic function		Busbar
Basic function accessories		Busbar for miniature circuit-breaker Busbar for residual-current circuit-breakers Busbar for combined residual-current/power circuit-breaker
Busbar type		Single phase
Product range		EVG

Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Phase busbar (ec@ss10.0.1-27-37-13-06 [ACN992011])			
Number of phases			1
Number of poles			1
Suitable for number of devices			6
Pitch dimensions		mm	0
Cross section		mm ²	10
Length		mm	104
Number of modular spacings			6
Rated permanent current I _u		A	63
Type of electric connection			Fork
Insulated			Yes
Rated surge voltage		kV	4
Conditioned rated short-circuit current I _q		kA	25
Max. rated operation voltage U _e		V	500
Rated short-time withstand current I _{cw}		kA	0
Suitable for devices with N-busbar			No
Suitable for devices with auxiliary switch			No